

MAXI® MAB SERIES

IN-LINE SCREW TERMINAL FUSE HOLDER



01520001TXN

Description

The MAXI® MAB Series 32V In-Line Screw Terminal Fuse Holder is designed to safely and easily replace hard-to-change fusible link wire. Compatible with up to 60-amp MAXI® blade fuses (sold separately), this automotive fuse holder is ideal for high-amp audio circuit protection.

An available dust cover helps safeguard the installed fuse from debris, while the interlocking fuse holder block feature allows 2-pole installation.

Web Resources

Download 2D print, installation guide and technical resources at: [littelfuse.com/MAB](https://www.littelfuse.com/MAB)

Ordering Information

| PART NUMBER | DESCRIPTION | CURRENT RATING MAX | FUSE TYPE | MOUNTING METHOD | MAX VOLTAGE RATING |
|----------------|---|--------------------|-----------|---------------------|--------------------|
| 01520001TXN | 32V In-Line Screw Terminal Fuse Holder - 100 Pcs. | 60 Amps | MAXI | In-Line Fuse Holder | 32V |
| 01520001TXN940 | 32V In-Line Screw Terminal Fuse Holder with Screws and Terminals - 200 Pcs. | 60 Amps | MAXI | In-Line Fuse Holder | 32V |
| 01520001TXN941 | 32V In-Line Screw Terminal Fuse Holder with Screws, Terminals, and Cover - 100 Pcs. | 60 Amps | MAXI | In-Line Fuse Holder | 32V |
| 01520001U | 32V In-Line Screw Terminal Fuse Holder - 500 Pcs. | 60 Amps | MAXI | In-Line Fuse Holder | 32V |
| 01520900H | Protective Fuse Holder Cover - 500 Pcs. | - | - | - | - |
| 01520900TXN | Protective Fuse Holder Cover - 500 Pcs. | - | - | - | - |
| 01520900U | Protective Fuse Holder Cover - 500 Pcs. | - | - | - | - |
| 0MAB0001F | 32V In-Line Screw Terminal Fuse Holder with Screws - 200 Pcs. | 60 Amps | MAXI | In-Line Fuse Holder | 32V |
| 0MAB0001XP | 32V In-Line Screw Terminal Fuse Holder with Screws - Blister Pack - 5 Pcs. | 60 Amps | MAXI | In-Line Fuse Holder | 32V |

Specifications

| | |
|-----------------------------|---|
| Current Rating Max: | 60 Amps |
| Fuse Type: | MAXI |
| Flammability Rating: | UL 94 V-2 |
| Input Terminals: | Recommended: 2.5 -6 MM ² (DIN 46234) 6 -10 MM ² (DIN 46234) |
| Mounting Method: | In-Line Fuse Holder Recommended: 2.5 -6 MM ² (DIN 46234) 6 -10 MM ² (DIN 46234) |
| Max Voltage Rating: | 32V |
| Wire Description: | Recommended: Cable Cross Section |
| Wire Size: | Recommended in MM²: 2.5, 4, 6 and 10 |

Applications

- High-Amp Audio Circuit Protection

Features and Benefits

- Compatible with MAXI® blade fuses up to 60 amps (sold separately)
- Interlocking fuse holder block feature enables 2-pole installation
- Screw terminals make in-line installation easy
- Available dust cover helps protect the installed fuse
- UL 94 V-2 flammability rating