

MINI® ADD-A-CIRCUIT® SERIES

FUSE HOLDER FOR MINI®, LOW PROFILE MINI®, OR MICRO2® FUSES



FHM20200ZPA



OFHM0200Z

Description

The MINI® Add-A-Circuit® Series Fuse Holder for MINI®, Low Profile MINI®, or MICRO2® Fuses is designed to allow easy installation of additional circuits without any cutting or splicing, which is typically necessary to prevent voiding a new vehicle warranty. The fuse tap turns a single fuse slot into two slots so you can protect the new accessory circuit as well as the existing circuit.

The MINI® Add-A-Circuit® fuse tap is available for MINI®, Low Profile MINI®, and MICRO2® fuses. Available blister packaged MINI® Add-A-Circuit® kits come with a set of fuses (3A, 5A, 7.5A, and 10A) in the corresponding MINI®, Low Profile MINI®, or MICRO2® fuse style.

Applications

- Add-On Accessory Circuits

Web Resources

Download 2D print, installation guide and technical resources at: littelfuse.com/MINI-AddACircuit

Ordering Information

| PART NUMBER | DESCRIPTION | CURRENT RATING MAX | FUSE TYPE | MOUNTING METHOD | MAX VOLTAGE RATING |
|--------------|---|--------------------|------------------|--|--------------------|
| OFHM0200S | 32V Fuse Holder for MINI® Fuses - UL-3266 (GPT) Lead with Butt Splice Connectors - 20-Pack | 10 Amps | MINI | In-Line Fuse Holder Blades / Butt Splice Connector | 32V |
| OFHM0200Z | 32V Fuse Holder for MINI® Fuses - UL-3266 (GPT) Lead with Butt Splice Connectors - Bulk | 10 Amps | MINI | In-Line Fuse Holder Blades / Butt Splice Connector | 32V |
| OFHM0200Z-NC | 32V Fuse Holder for MINI® Fuses - UL-3266 (GPT) Lead, No Connector - Bulk | 10 Amps | MINI | In-Line / Fuse Holder Blades | 32V |
| OFHM0200ZP | 32V Fuse Holder for MINI® Fuses - UL-3266 (GPT) Lead with Butt Splice Connectors - Blister Packaged Kit with Fuses | 10 Amps | MINI | In-Line Fuse Holder Blades / Butt Splice Connector | 32V |
| FHLM0200Z | 58V Fuse Holder for Low Profile MINI® Fuses - UL 1015 Lead with Butt Splice Connectors - Bulk | 10 Amps | LOW PROFILE MINI | In-Line Fuse Holder Blades / Butt Splice Connector | 58V |
| FHLM0200ZPA | 58V Fuse Holder for Low Profile MINI® Fuses - UL 1015 Lead with Butt Slice Connectors - Blister Packaged Kit with Fuses | 10 Amps | LOW PROFILE MINI | In-Line Fuse Holder Blades / Butt Splice Connector | 58V |
| FHM20200Z | 32V Fuse Holder for MICRO2® Fuses - GXL Lead with Butt Splice Connectors - Bulk | 10 Amps | MICRO2 | Blade Type Mounting With Cable And Butt Splice Connector | 32V |
| FHM20200ZPA | 32V Fuse Holder for MICRO2® Fuses - GXL Leads with Butt Splice Connectors - Blister Packaged Kit with Fuses | 10 Amps | MICRO2 | Blade Type Mounting With Cable And Butt Splice Connector | 32V |

Specifications

| | |
|-------------------------------------|--|
| Current Rating Continuous: | 7.5 Amps |
| Current Rating Max: | 10 Amps |
| Current Rating Max Terminal: | 10 Amps |
| Fuse Type: | Low Profile MINI / MICRO2 Fuse / MINI |
| Flammability Rating: | UL 94 V-0 |
| Input Terminals: | Butt Splice Connectors In Line |
| Mounting Method: | In-Line Fuse Holder Blades / Butt Splice Connector In-Line / Fuse Holder Blades |
| Output Terminals: | Fuse Holder Blades |
| Max Voltage Rating: | 32 VDC / 58 VDC |
| Wire Description: | 125°C rated, UL-3266 (GPT) RED Wire, Stranded Copper UL 1015 Red Wire Withstand 105°C GXL Red Wire Withstand 125°C |
| Wire Size: | 16 AWG |

Features and Benefits

- Available for MINI®, Low Profile MINI®, and MICRO2® fuses
- Turns one fuse slot into two to protect an additional accessory circuit without cutting or splicing
- Available butt splice connectors allow easy wiring
- 16 AWG wire leads with red insulation
- UL 94 V-0 flammability rating