



RESISTANCE @ +25°C = 10,000 Ω ± 2%  
 RESISTANCE/TEMPERATURE CURVE = "G"  
 BETA "β" (0 TO +50°C) = 3,575°K NOMINAL  
 TEMPERATURE COEFFICIENT @ +25°C = -4.04%/°C NOMINAL  
 DISSIPATION CONSTANT = 3 mW/°C NOMINAL  
 THERMAL TIME CONSTANT = 15 SECONDS MAXIMUM (STILL AIR)  
 THERMAL TIME CONSTANT = 3 SECONDS MAXIMUM (STIRRED OIL)  
 MAXIMUM TEMPERATURE RATING = +150°C

---	ISO RELEASE	04/16/03	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	<b>U.S. SENSOR CORP.</b> 1832 W. COLL INS AVE. ORANGE, CA . 92867 714-639-1000 www.ussensor.com
DRAWN BY	T. WILFONG	
DATE	04/22/97	
REV.	NONE	
LAYER	0 OF 1	
		NTC THERMISTOR
		P/N DC103G9G