



RESISTANCE @ +25°C = 10,000 ± 10%
 RESISTANCE/TEMPERATURE CURVE = "E1"
 BETA "β" (+25 TO +85°C) = 3,435°K NOMINAL
 TEMPERATURE COEFFICIENT @ +25°C = -3.82%/°C NOMINAL
 DISSIPATION CONSTANT = 0.7 mW/°C NOMINAL (AIR)
 THERMAL TIME CONSTANT = 5 SECONDS NOMINAL (AIR)
 MAXIMUM TEMPERATURE RATING = +300°C

SEE MANUFACTURING SPECIFICATION (LAYER 1)

| | | | |
|------|-----------------------|----------|-----|
| NONE | RELEASE TO PRODUCTION | 03/18/14 | DD |
| REV | REVISION RECORD | DATE | APP |

| | |
|----------------------|---|
| SCALE NONE | U.S. SENSOR CORP. © COPYRIGHT 714-639-1000 www.ussensor.com NTC THERMISTOR P/N GS103E1K |
| DRAWN BY DAN DANKERT | |
| DATE 03/18/14 | |
| REV. NONE | |
| LAYER 0 OF 2 | |