



RESISTANCE @ +25°C = 2,500 Ω ± 10%  
 RESISTANCE/TEMPERATURE CURVE = "F"  
 TEMPERATURE COEFFICIENT @ +25°C = -3.86%/°C NOMINAL  
 BETA "β" (0 TO +50°C) = 3,419°K NOMINAL  
 DISSIPATION CONSTANT = 2 mW/°C NOMINAL (STILL AIR)  
 THERMAL TIME CONSTANT = 5 SECONDS NOMINAL (STILL AIR)  
 THERMAL TIME CONSTANT = 0.5 SECONDS NOMINAL (WELL STIRRED OIL)  
 MAXIMUM TEMPERATURE RATING = +300°C

|     |  |          |     |
|-----|--|----------|-----|
| --- | ISO RELEASE  | 10/20/03 | DD  |
| "A" | WIRE DIA WAS 0.020"±0.001", WIRE LENGTH WAS 1.125" NOM | 10/20/03 | DD  |
| REV | REVISION RECORD  | DATE     | APP |

|                         |  |
|-------------------------|--|
| SCALE NONE              | © COPYRIGHT<br><b>U.S. SENSOR CORP.</b><br>714-639-1000 www.ussensor.com<br><b>NTC THERMISTOR</b><br>P/N 252FG1K |
| DRAWN BY<br>DAN DANKERT |  |
| DATE 03/27/90           |  |
| REV. "A"                |  |
| LAYER 0 OF 1            |  |