



RESISTANCE @ +25°C = 500 Ω ± 10%
 RESISTANCE/TEMPERATURE CURVE = "F"
 TEMPERATURE COEFFICIENT @ +25°C = -3.86%/°C NOMINAL
 BETA "β" (0 TO +50°C) = 3,419°K NOMINAL
 DISSIPATION CONSTANT = 3 mW/°C NOMINAL (STILL AIR)
 THERMAL TIME CONSTANT = 8 SECONDS MAXIMUM (STILL AIR)
 THERMAL TIME CONSTANT = 2 SECONDS MAXIMUM (WELL STIRRED OIL)
 MAXIMUM TEMPERATURE RATING = +300°C

| | | | |
|-----|----------------------------|----------|-----|
| "A" | LEAD WIRE GAUGE WAS 20 AWG | 12/08/03 | DD |
| --- | ISO RELEASE | 12/08/03 | DD |
| REV | REVISION RECORD | DATE | APP |

| | |
|-------------------------|------------------------------------------------------------------------------------------------------------------|
| SCALE NONE | © COPYRIGHT U.S. SENSOR CORP. 714-639-1000 www.ussensor.com NTC THERMISTOR P/N 501FH1K |
| DRAWN BY DAN DANKERT | |
| DATE 10/02/02 | |
| REV. "A" | |
| LAYER 0 OF 1 | |