


LGB8204ATH

400 V, 18 A N-Channel Ignition IGBT



Product Summary

| Characteristic | Value | Unit |
|----------------|-------|------|
| V_{CES} | 400 | V |
| I_c | 18 | A |

Description


This Logic Level Insulated Gate Bipolar Transistor (IGBT) features monolithic circuitry integrating ESD and Over-Voltage clamped protection for use in inductive coil drivers applications. Primary uses include Ignition, Direct Fuel Injection, or wherever high voltage and high current switching is required.

Agency Approvals

Environmental Approvals




Pinout Diagram



Features

- Ideal for Coil-on-Plug Applications
- Gate-Emitter ESD Protection
- Temperature Compensated Gate-Collector Voltage Clamp Limits Stress Applied to Load
- Integrated ESD Diode Protection
- New Design Increases Unclamped Inductive Switching (UIS) Energy Per Area
- Low Threshold Voltage Interfaces Power Loads to Logic or Microprocessor Devices
- Low Saturation Voltage
- High Pulsed Current Capability
- Integrated Gate-Emitter Resistor (R_{GE})
- AEC-Q101 Qualified
- These are Pb-Free Devices
- Emitter Ballasting for Short-Circuit Capability

Functional Diagram



| | |
|---|----|
| 1. Maximum Ratings ($T_J = 25\text{ }^\circ\text{C}$ unless otherwise specified) | 3 |
| 2. Unclamped Collector-to-Emitter Avalanche Characteristics | 3 |
| 3. Maximum Short-Circuit Times | 3 |
| 4. Thermal Characteristics | 3 |
| 5. Electrical Characteristics – Off | 4 |
| 6. Electrical Characteristics – On | 4 |
| 7. Dynamic Characteristics | 5 |
| 8. Switching Characteristics | 5 |
| 9. Figure Data | 6 |
| 10. Package Dimensions | 9 |
| 11. Part Numbering and Marking | 10 |
| 12. Packing Options | 10 |

1. Maximum Ratings ($T_J = 25\text{ }^\circ\text{C}$ unless otherwise specified)

| Characteristic | Conditions | Symbol | Value | Unit |
|---|---|----------------|-------------|---------------------------|
| Collector-Emitter Voltage | - | V_{CES} | 430 | V_{DC} |
| Collector-Gate Voltage | - | V_{CER} | 430 | V_{DC} |
| Gate-Emitter Voltage | - | V_{GE} | 18 | V_{DC} |
| Collector Current – Continuous | $T_C = 25\text{ }^\circ\text{C}$ | I_C | 18 | A_{DC} |
| Collector Current – Pulsed | | | 50 | A_{AC} |
| ESD – Human Body Model | $R = 1500\ \Omega, C = 100\ \text{pF}$ | ESD | 8.0 | kV |
| ESD – Machine Model | $R = 0\ \Omega, C = 200\ \text{pF}$ | | 800 | V |
| Total Power Dissipation | $T_C = 25\text{ }^\circ\text{C}$ | P_D | 115 | W |
| | Derating for $> 25\text{ }^\circ\text{C}$ | | 0.77 | $\text{W}/^\circ\text{C}$ |
| Operating and Storage Temperature Range | - | T_J, T_{stg} | -55 to +175 | $^\circ\text{C}$ |

2. Unclamped Collector-to-Emitter Avalanche Characteristics

| Characteristic | Symbol | Value | Unit |
|--|-------------|-------|------|
| Single Pulse Collector-to-Emitter Avalanche Energy | | | |
| $V_{CC} = 50\ \text{V}, V_{GE} = 5.0\ \text{V}, P_{kL} = 21.1\ \text{A}, L = 1.8\ \text{mH}, \text{Starting } T_J = 25\text{ }^\circ\text{C}$ | E_{AS} | 400 | mJ |
| $V_{CC} = 50\ \text{V}, V_{GE} = 5.0\ \text{V}, P_{kL} = 18.3\ \text{A}, L = 1.8\ \text{mH}, \text{Starting } T_J = 125\text{ }^\circ\text{C}$ | | 300 | |
| Reverse Avalanche Energy | | | |
| $V_{CC} = 100\ \text{V}, V_{GE} = 20\ \text{V}, P_{kL} = 25.8\ \text{A}, L = 6.0\ \text{mH}, \text{Starting } T_J = 25\text{ }^\circ\text{C}$ | $E_{AS(R)}$ | 2000 | mJ |

Note: $-55\text{ }^\circ\text{C} \leq T_J \leq 150\text{ }^\circ\text{C}$

3. Maximum Short-Circuit Times

| Characteristic | Symbol | Value | Unit |
|---|------------|-------|---------------|
| Short Circuit Withstand Time ¹ | $t_{sc,1}$ | 750 | μs |
| Short Circuit Withstand Time ² | $t_{sc,2}$ | 5.0 | ms |

Note: $-55\text{ }^\circ\text{C} \leq T_J \leq 150\text{ }^\circ\text{C}$

Footnote 1: See Figure 17, 3 pulses with 10 ms period

Footnote 2: See Figure 18, 3 pulses with 10 ms period

4. Thermal Characteristics

| Characteristic | Symbol | Value | Unit |
|---|-----------------|-------|---------------------------|
| Thermal Resistance, Junction to Case | $R_{\theta JC}$ | 1.3 | $^\circ\text{C}/\text{W}$ |
| Thermal Resistance, Junction to Ambient (D2PAK) ³ | $R_{\theta JA}$ | 50 | $^\circ\text{C}/\text{W}$ |
| Maximum Lead Temperature for Soldering Purposes, 1/8" from case for 5 seconds | T_L | 275 | $^\circ\text{C}$ |

Footnote 3: When surface mounted to an FR4 board using the minimum recommended pad size

5. Electrical Characteristics – Off

| Characteristic | Symbol | Conditions | Temperature | Value | | | Unit |
|---|----------------------|--|-----------------------------------|-------|-----|-----------------|------------------|
| | | | | Min | Typ | Max | |
| Collector-Emitter Clamp Voltage | BV _{CES} | I _C = 2.0 mA | T _J = -40 °C to 150 °C | 380 | 395 | 420 | V _{DC} |
| | | I _C = 10 mA | | 390 | 405 | 430 | |
| Zero Gate Voltage Collector Current | I _{CES} | V _{GE} = 200 V, V _{GE} = 0 V | T _J = 25 °C | - | 2.0 | 10 | μA _{DC} |
| | | | T _J = 150 °C | - | 10 | 40 ⁴ | |
| | | | T _J = -40 °C | - | 1.0 | 10 | |
| Reverse Collector-Emitter Leakage Current | I _{ECS} | V _{CE} = -24 V | T _J = 25 °C | - | 0.7 | 1.0 | mA |
| | | | T _J = 150 °C | - | 12 | 25 ⁴ | |
| | | | T _J = -40 °C | - | 0.1 | 1.0 | |
| Reverse Collector-Emitter Clamp Voltage | BV _{CES(R)} | I _C = -75 mA | T _J = 25 °C | 27 | 33 | 37 | V _{DC} |
| | | | T _J = 150 °C | 30 | 36 | 40 | |
| | | | T _J = -40 °C | 25 | 32 | 35 | |
| Gate-Emitter Clamp Voltage | BV _{GES} | I _G = 5.0 mA | T _J = -40 °C to 150 °C | 11 | 13 | 15 | V _{DC} |
| Gate-Emitter Leakage Current | I _{GES} | V _{GE} = 10 V | T _J = -40 °C to 150 °C | 384 | 640 | 700 | μA _{DC} |
| Gate-Emitter Resistor | R _{GE} | - | T _J = -40 °C to 150 °C | 10 | 16 | 26 | kΩ |

Footnote 4: Maximum value of characteristic across temperature range

6. Electrical Characteristics – On

| Characteristic | Symbol | Conditions | Temperature | Value | | | Unit |
|--|-------------------------|---|-----------------------------------|------------------|------|------------------|-----------------|
| | | | | Min | Typ | Max | |
| Gate Threshold Voltage | V _{GE(th)} | I _C = 1.0 mA, V _{GE} = V _{CE} | T _J = 25 °C | 1.1 | 1.4 | 1.9 | V _{DC} |
| | | | T _J = 150 °C | 0.75 | 1.0 | 1.4 | |
| | | | T _J = -40 °C | 1.2 | 1.6 | 2.1 ⁴ | |
| Threshold Temperature Coefficient (Negative) | - | - | - | - | 3.4 | - | mV/°C |
| Collector-Emitter On-Voltage ⁵ | V _{CE(on)} | I _C = 6.0 A, V _{GE} = 4.0 V | T _J = 25 °C | 1.0 | 1.4 | 1.6 | V _{DC} |
| | | | T _J = 150 °C | 0.9 | 1.3 | 1.6 | |
| | | | T _J = -40 °C | 1.1 | 1.45 | 1.7 ⁴ | |
| | | I _C = 8.0 A, V _{GE} = 4.0 V | T _J = 25 °C | 1.3 | 1.6 | 1.9 ⁴ | |
| | | | T _J = 150 °C | 1.2 | 1.55 | 1.8 | |
| | | | T _J = -40 °C | 1.4 | 1.6 | 1.9 ⁴ | |
| | | I _C = 10 A, V _{GE} = 4.0 V | T _J = 25 °C | 1.4 | 1.8 | 2.0 | |
| | | | T _J = 150 °C | 1.5 | 1.8 | 2.0 | |
| | | | T _J = -40 °C | 1.4 | 1.8 | 2.1 ⁴ | |
| | | I _C = 15 A, V _{GE} = 4.0 V | T _J = 25 °C | 1.8 | 2.2 | 2.5 | |
| | | | T _J = 150 °C | 2.0 | 2.4 | 2.6 | |
| | | | T _J = -40 °C | 1.7 | 2.1 | 2.5 | |
| I _C = 10 A, V _{GE} = 4.5 V | T _J = 25 °C | 1.3 | 1.8 | 2.0 ⁴ | | | |
| | T _J = 150 °C | 1.3 | 1.75 | 2.0 ⁴ | | | |
| | T _J = -40 °C | 1.4 | 1.8 | 2.0 ⁴ | | | |
| Forward Transconductance ⁵ | gfs | V _{CS} = 5.0 V, I _C = 6.0 A | T _J = -40 °C to 150 °C | 8.0 | 14 | 25 | Mhos |

Footnote 4: Maximum value of characteristic across temperature range

Footnote 5: Pulse Test: Pulse Width ≤ 300 μs, Duty Cycle ≤ 2%

7. Dynamic Characteristics

| Characteristic | Symbol | Conditions | Temperature | Value | | | Unit |
|----------------------|-----------|--|---|-------|-----|------|------|
| | | | | Min | Typ | Max | |
| Input Capacitance | C_{ISS} | $V_{CC} = 25\text{ V}, V_{GE} = 0\text{ V},$ $f = 1.0\text{ MHz}$ | $T_J = -40\text{ }^\circ\text{C to } 150\text{ }^\circ\text{C}$ | 400 | 800 | 1000 | pF |
| Output Capacitance | C_{OSS} | | | 50 | 75 | 100 | |
| Transfer Capacitance | C_{RSS} | | | 4.0 | 7.0 | 10 | |

8. Switching Characteristics

| Characteristic | Symbol | Conditions | Temperature | Value | | | Unit |
|---------------------------------|--------------|--|----------------------------------|-------|-----|-----|---------------|
| | | | | Min | Typ | Max | |
| Turn-off Delay Time (Resistive) | $t_{d(off)}$ | $V_{CC} = 300\text{ V}, I_C = 6.5\text{ A},$ $R_G = 1.0\text{ k}\Omega, R_L = 46\text{ }\Omega$ | $T_J = 25\text{ }^\circ\text{C}$ | - | 4.0 | 10 | μs |
| Fall Time (Resistive) | t_f | | | - | 9.0 | 15 | |
| Turn-on Delay Time | $t_{d(on)}$ | $V_{CC} = 10\text{ V}, I_C = 6.5\text{ A},$ $R_G = 1.0\text{ k}\Omega, R_L = 1.5\text{ }\Omega$ | $T_J = 25\text{ }^\circ\text{C}$ | - | 0.7 | 4.0 | μs |
| Rise Time | t_r | | | - | 4.5 | 7.0 | |

9. Figure Data

Figure 1. Output Characteristics ($T_J = 25\text{ }^\circ\text{C}$)




Figure 2. Output Characteristics ($T_J = -40\text{ }^\circ\text{C}$)




Figure 3. Output Characteristics ($T_J = 150\text{ }^\circ\text{C}$)




Figure 4. Transfer Characteristics




Figure 5. Collector-Emitter Saturation Voltage vs. Junction Temperature




Figure 6. Collector-Emitter Voltage vs. Gate-Emitter Voltage ($T_J = 25\text{ }^\circ\text{C}$)




Figure 7. Collector-Emitter Voltage vs. Gate-Emmitter Voltage ($T_J = 150\text{ }^\circ\text{C}$)




Figure 8. Capacitance Variation




Figure 9. Gate Threshold Voltage vs. Temperature




Figure 10. Minimum Open Secondary Latch Current vs. Temperature




Figure 11. Typical Open Secondary Latch Current vs. Temperature




Figure 12. Inductive Switching Fall Time vs. Temperature




Figure 13. Single Pulse Safe Operating Area
(Mounted on an Infinite Heatsink at $T_A = 25^\circ\text{C}$)




Figure 14. Single Pulse Safe Operating Area
(Mounted on an Infinite Heatsink at $T_A = 125^\circ\text{C}$)




Figure 15. Pulse Train Safe Operating Area
(Mounted on an Infinite Heatsink at $T_A = 25^\circ\text{C}$)




Figure 16. Pulse Train Safe Operating Area
(Mounted on an Infinite Heatsink at $T_A = 125^\circ\text{C}$)




Figure 17. Circuit Configuration for Short Circuit Test 1




Figure 18. Circuit Configuration for Short Circuit Test 2






Figure 19. Transient Thermal Resistance

(Non-normalized Junction-Ambient mounted on minimum pad area)




10. Package Dimensions



| Symbol | Millimeters | | |
|--------|-------------|-----|--------|
| | Min | Nom | Max |
| A | 4.360 | - | 4.560 |
| A1 | 0.000 | - | 0.250 |
| b | 0.700 | - | 0.900 |
| b1 | 0.510 | - | 0.890 |
| b2 | 1.200 | - | 1.460 |
| b3 | 1.170 | - | 1.370 |
| c | 0.380 | - | 0.694 |
| c1 | 0.380 | - | 0.534 |
| c2 | 1.190 | - | 1.340 |
| D | 8.600 | - | 9.000 |
| D1 | 6.900 | - | 7.500 |
| E | 10.150 | - | 10.550 |
| E1 | 8.100 | - | 8.700 |
| e | 2.540 BSC | | |
| H | 15.000 | - | 15.600 |
| L | 1.900 | - | 2.500 |
| L1 | - | - | 1.650 |
| L2 | - | - | 1.780 |
| L3 | 0.250 | | |
| L4 | 4.780 | - | 5.280 |
| J1 | 2.560 | - | 2.960 |


Recommended Solder Pad Layout:



Notes:

1. Dimensioning & tolerancing confirm to ASME Y14.5M-1994.
2. All dimensions are in millimeters. Angles are in degrees.
3. Heatsink side flash is max 0.8 mm.
4. Radius on terminal is optional

11. Part Numbering and Marking



GB8204x = Device Code
 A = Assembly Location
 XX = Lot Number
 Y = Year
 WW = Work Week
 H = Ballast Structure Design

12. Packing Options

| Part Number | Package | Packing Mode | M.O.Q. |
|-------------|-----------------|--------------|--------|
| LGB8204ATH | D2PAK (Pb-Free) | Tape & Reel | 800 |

For additional information please visit www.Littelfuse.com/powersemi

Disclaimer Notice - Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly forth in applicable Littelfuse product documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation.

Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics