



### DST2080S



#### Pin out



#### Description

Littelfuse DST series Ultra Low  $V_F$  Schottky Barrier Rectifier is designed to meet the general requirements of commercial and industry applications by providing high temperature, low leakage and lower  $V_F$  products.

It is suitable for high frequency switching mode power supply, free-wheeling diodes and polarity protection diodes.

#### Features

- Ultra low forward voltage drop
- High frequency operation
- MSL: Level 1 - unlimited
- High junction temperature capability
- Trench MOS Schottky technology
- Single die in TO-277B Package
- Pb-free E3 means 2nd level interconnect is Pb-free and the terminal finish material is tin(Sn) (IPC/ JEDEC J-STD-609A.01)

#### Applications

- Switching mode power supply
- DC/DC converters
- Free-Wheeling diodes
- Polarity Protection Diodes

#### Maximum Ratings

| Parameters  | Symbol      | Test Conditions   | Max | Unit |
|---|-------------|---|-----|------|
| Peak Inverse Voltage                                  | $V_{RWM}$   | -   | 80  | V    |
| Average Forward Current (per device) *                | $I_{F(AV)}$ | 50% duty cycle @ $T_A = 85^\circ\text{C}$ rectangular wave form | 20  | A    |
| Peak One Cycle Non-Repetitive Surge Current (per leg) | $I_{FSM}$   | 8.3 ms, half Sine pulse   | 150 | A    |

\* Mounted on 30 mm x 30 mm pad areas aluminum PCB

#### Electrical Characteristics


| Parameters                       | Symbol   | Test Conditions                                      | Typ  | Max  | Unit          |
|----------------------------------|----------|--|------|------|---------------|
| Forward Voltage Drop (per leg) * | $V_{F1}$ | @10A, Pulse, $T_J = 25^\circ\text{C}$                | 0.52 | -    | V             |
|                                  |          | @20A, Pulse, $T_J = 25^\circ\text{C}$                | 0.64 | 0.70 |               |
|                                  | $V_{F2}$ | @10A, Pulse, $T_J = 125^\circ\text{C}$               | 0.46 | -    |               |
|                                  |          | @20A, Pulse, $T_J = 125^\circ\text{C}$               | 0.60 | 0.65 |               |
| Reverse Current (per leg) *      | $I_{R1}$ | @ $V_R = \text{rated } V_R, T_J = 25^\circ\text{C}$  | 22   | 300  | $\mu\text{A}$ |
|                                  | $I_{R2}$ | @ $V_R = \text{rated } V_R, T_J = 125^\circ\text{C}$ | 11   | 75   | mA            |

\* Pulse Width < 300 $\mu\text{s}$ , Duty Cycle < 2%


### Thermal-Mechanical Specifications

| Parameters  | Symbol      | Test Conditions | Max         | Unit |
|---|-------------|-----------------|-------------|------|
| Junction Temperature                              | $T_J$       |                 | -55 to +150 | °C   |
| Storage Temperature                               | $T_{stg}$   |                 | -55 to +150 | °C   |
| Typical Thermal Resistance<br>Junction to Ambient | $R_{th,JA}$ | DC operation    | 70          | °C/W |
| Approximate Weight                                | wt          |                 | 0.08        | g    |
| Case Style  |             | TO-277B         |             |      |


**Figure 1: Typical Forward Characteristics**




**Figure 2: Typical Reverse Characteristics**



**Figure 3: Typical Junction Capacitance**




### Dimensions-TO-277B




| Symbol | Millimeters |      |      |
|--------|-------------|------|------|
|        | Min         | Typ  | Max  |
| A      | 6.30        | 6.50 | 6.70 |
| B      | 5.28        | 5.38 | 5.48 |
| C      | 3.88        | 3.98 | 4.08 |
| D      | 2.90        | 3.05 | 3.20 |
| E      | 3.40        | 3.55 | 3.70 |
| F      | 4.20        | 4.40 | 4.60 |
| G      | 1.70        | 1.80 | 1.90 |
| I      | 1.74        | 1.84 | 1.94 |
| J      | 0.65        | 0.85 | 1.05 |
| K      | 0.85        | 0.90 | 0.95 |
| L      | 0.95        | 1.10 | 1.25 |
| M      | 0.20        | 0.25 | 0.30 |
| N      | 0.25        | 0.40 | 0.55 |
| O      | 4.00        | 4.05 | 4.25 |

### Mounting Pad Layout



### Part Numbering and Marking System




DST = Device Type  
 20 = Forward Current (20A)  
 80 = Reverse Voltage (80V)  
 S = Package Type  
 LF = Littelfuse  
 YY = Year  
 WW = Week  
 L = Lot Number

### Packing Options

| Part Number | Marking  | Packing Mode   | M.O.Q |
|-------------|----------|----------------|-------|
| DST2080S    | DST2080S | 5000pcs / Reel | 5000  |

### Carrier Tape & Reel Specification



| Symbol | Millimeters |       |
|--------|-------------|-------|
|        | Min         | Max   |
| A      | 4.28        | 4.48  |
| B      | 6.80        | 7.00  |
| d      | 1.40        | 1.60  |
| d1     | -           | 1.50  |
| E      | 1.65        | 1.85  |
| F      | 5.40        | 5.60  |
| P      | 7.90        | 8.10  |
| P0     | 3.90        | 4.10  |
| W      | 11.70       | 12.30 |