



RESISTANCE @ +25°C = 10,000 Ω ± 1%
 BETA "β" (0 TO +50°C) = 3,892°K NOMINAL
 RESISTANCE/TEMPERATURE CURVE = "J"
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL
 THERMAL TIME CONSTANT = 15 SECONDS MAXIMUM (STILL AIR)
 THERMAL TIME CONSTANT = 3 SECONDS MAXIMUM (STIRRED OIL)
 DISSIPATION CONSTANT = 3 mW/°C NOMINAL
 MAXIMUM OPERATING TEMPERATURE = +150°C

---	ISO RELEASE	06/10/03	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	U.S. SENSOR CORP. 1832 W. COLLINS AVE. ORANGE, CA . 92867 714-639-1000 www.ussensor.com
DRAWN BY	DAN DANKERT	
DATE	04/05/99	
REV.	NONE	
LAYER	0 OF 1	
		NTC THERMISTOR
		P/N DC103J2F