



RESISTANCE @ +25°C = 1,000 Ω ± 10%  
 RESISTANCE/TEMPERATURE CURVE = "F"  
 TEMPERATURE COEFFICIENT @ +25°C = -3.86%/°C NOMINAL  
 BETA "β" (0 TO +50°C) = 3,419°K NOMINAL  
 DISSIPATION CONSTANT = 1 mW/°C NOMINAL  
 THERMAL TIME CONSTANT = 10 SECONDS MAXIMUM (STILL AIR)  
 THERMAL TIME CONSTANT = 1 SECOND MAXIMUM (WELL STIRRED OIL)  
 MAXIMUM TEMPERATURE RATING = +135°C

| REV | REVISION RECORD | DATE     | APP |
|-----|-----------------|----------|-----|
| --- | ISO RELEASE     | 10/20/03 | DD  |
|     |                 |          |     |
|     |                 |          |     |

|                         |   |
|-------------------------|---|
| SCALE NONE              | © COPYRIGHT<br>U.S. SENSOR CORP.<br>714-639-1000 www.ussensor.com |
| DRAWN BY<br>DAN DANKERT |   |
| DATE 08/28/96           | NTC THERMISTOR  |
| REV. NONE               | P/N KC102F2K  |
| LAYER 0 OF 1            |   |