


22 AWG (0.0256" ± 0.003" DIAMETER),  
TINNED CCS, 1.00" LONG MINIMUM



RESISTANCE @ +25°C = 2,000 Ω ± 10%  
 RESISTANCE TEMPERATURE CURVE = "J"  
 BETA "β" (0 TO +50°C) = 3,892°K NOMINAL  
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL  
 DISSIPATION CONSTANT = 3 mW/°C NOMINAL (STILL AIR)  
 THERMAL TIME CONSTANT = 8 SECONDS NOMINAL (STILL AIR)  
 THERMAL TIME CONSTANT = 2 SECONDS NOMINAL (STIRRED OIL)  
 MAXIMUM TEMPERATURE RATING = +300°C

\*\*\* ROHS COMPLIANT \*\*\*

SEE MANUFACTURING SPECIFICATION (LAYER 1)

|      |                       |          |     |
|------|-----------------------|----------|-----|
| NONE | RELEASE TO PRODUCTION | 01/27/14 | DD  |
| REV  | REVISION RECORD       | DATE     | APP |

|          |             |   |
|----------|-------------|---|
| SCALE    | NONE        | © COPYRIGHT<br><b>U.S. SENSOR CORP.</b><br>714-639-1000 www.ussensor.com<br><b>NTC THERMISTOR</b><br><b>P/N 202JH1K</b> |
| DRAWN BY | DAN DANKERT |   |
| DATE     | 01/27/14    |   |
| REV      | NONE        |   |
| LAYER    | 0 OF 2      |   |