


# SiC Schottky Diode


 $V_{RRM} = 1200\text{ V}$   
 $I_{FAV} = 2 \times 60\text{ A}$ 

Ultra fast switching  
 Zero reverse recovery

Part number  
**DCG130X1200NA**



Backside: isolated

 E72873


### Features / Advantages:

- Ultra fast switching
- Zero reverse recovery
- Zero forward recovery
- Temperature independent switching behavior
- Positive temperature coefficient of forward voltage
- $T_{VJM} = 175^{\circ}\text{C}$

### Applications:

- Solar inverter
- Uninterruptible power supply (UPS)
- Welding equipment
- Switched-mode power supplies
- Medical equipment
- High speed rectifier

### Package: SOT-227B (minibloc)

- Isolation Voltage: 2500 V~
- Industry standard outline
- RoHS compliant
- Epoxy meets UL 94V-0
- Base plate with Aluminium nitride isolation for low thermal resistance
- Advanced power cycling

### Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).


SiC Diode (per leg)				Ratings		
Symbol	Definitions	Conditions	min.	typ.	max.	
$V_{RSM}$	max. non-repetitive reverse blocking voltage				1200	V
$V_{RRM}$	max. repetitive reverse blocking voltage				1200	V
$I_R$	reverse current	$V_R = V_{RRM}$		140 480	800 1200	$\mu$ A $\mu$ A
$V_F$	forward voltage	$I_F = 30$ A	$T_{VJ} = 25^\circ\text{C}$	1.3		V
		$I_F = 60$ A	$T_{VJ} = 175^\circ\text{C}$	1.6	1.8	V
$I_{FAV}$	average forward current	$I_F = 30$ A	$T_{VJ} = 175^\circ\text{C}$	1.55		V
		$I_F = 60$ A		2.3	3	V
$I_{F25}$	forward current	$T_C = 80^\circ\text{C}$ $T_C = 100^\circ\text{C}$	} rectangular d = 0.5	$T_{VJ} = 175^\circ\text{C}$	60	A
					53	A
$I_{F80}$			$T_C = 25^\circ\text{C}$		105	A
$I_{F100}$			$T_C = 80^\circ\text{C}$		81	A
$I_{F100}$			$T_C = 100^\circ\text{C}$		71	A
$I_{FSM}$	max forward surge current	t = 10 ms, 1/2 sine (50 Hz), $V_R = 0$ V $t_p = 10$ $\mu$ s, pulse, $V_R = 0$ V	$T_{VJ} = 25^\circ\text{C}$		1150	A A
$V_{F0}$	threshold voltage	} for power loss calculation	$T_{VJ} = 125^\circ\text{C}$	0.80		V
$r_F$	slope resistance		$T_{VJ} = 175^\circ\text{C}$	0.73		V
$Q_C$	total capacitive charge	$V_R = 800$ V, $I_F = 60$ A dI/dt = 800 A/ $\mu$ s	$T_{VJ} = 25^\circ\text{C}$	20.0		m $\Omega$
				24.6		m $\Omega$
$C$	total capacitance	$V_R = 0$ V $V_R = 400$ V $V_R = 800$ V	} f = 1 MHz	$T_{VJ} = 25^\circ\text{C}$	4500	pF
					280	pF
					200	pF
$R_{thJC}$	thermal resistance junction to case				0.43	K/W
$R_{thJH}$	thermal resistance junction to heatsink	with heatsink compound; IXYS test setup			0.55	K/W



Package Outlines SOT-227B (minibloc)			Ratings			
Symbol	Definitions	Conditions	min.	typ.	max.	Unit
$I_{RMS}$	RMS current	per terminal			100	A
$T_{stg}$	storage temperature		-40		150	°C
$T_{op}$	operation temperature		-40		150	°C
$T_{VJ}$	virtual junction temperature		-40		175	°C
<b>Weight</b>				30		g
$M_D$	mounting torque <sup>1)</sup>	screws to heatsink terminal connection screws			1.5 1.3	Nm Nm
$d_{Spp}$	creepage distance on surface	terminal to terminal	10.5			mm
$d_{Spb}$		terminal to backside	8.5			mm
$d_{App}$	striking distance through air	terminal to terminal	3.2			mm
$d_{Apb}$		terminal to backside	6.8			mm
$V_{ISOL}$	isolation voltage	$I_{ISOL} \leq 1 \text{ mA}; 50/60 \text{ Hz}$	3000 2500			V V
$C_p$	coupling capacity per switch	between shorted terminals of one diode and back side metallization		20		pF

<sup>1)</sup> further information see application note IXAN0073 on [www.ixys.com/TechnicalSupport/appnotes.aspx](http://www.ixys.com/TechnicalSupport/appnotes.aspx) (General / Isolation, Mounting, Soldering, Cooling)

**Product Marking**




**Part description**

- D = Diode
- C = SiC
- G = Extreme fast
- 130 = Current Rating [A]
- X = Parallel legs
- 1200 = Reverse Voltage [V]
- NA = SOT-227 (minibloc)


Ordering	Part Name	Marking on Product	Delivering Mode	Base Qty	Ordering Code
Standard	DCG130X1200NA	DCG130X1200NA	Tube	10	DCG130X1200NA

**Equivalent Circuits for Simulation** *\*on die level, typical*

		$T_{VJ} = 125^\circ\text{C}$	$T_{VJ} = 175^\circ\text{C}$	
$V_{0 \max}$	threshold voltage	0.80	0.73	V
$R_{0 \max}$	slope resistance *	20.0	24.6	mΩ

**Outlines SOT-227B (minibloc)**


Dim.	Millimeter		Inches	
	min	max	min	max
A	31.50	31.88	1.240	1.255
B	7.80	8.20	0.307	0.323
C	4.09	4.29	0.161	0.169
D	4.09	4.29	0.161	0.169
E	4.09	4.29	0.161	0.169
F	14.91	15.11	0.587	0.595
G	30.12	30.30	1.186	1.193
H	37.80	38.23	1.488	1.505
J	11.68	12.22	0.460	0.481
K	8.92	9.60	0.351	0.378
L	0.74	0.84	0.029	0.033
M	12.50	13.10	0.492	0.516
N	25.15	25.42	0.990	1.001
O	1.95	2.13	0.077	0.084
P	4.95	6.20	0.195	0.244
Q	26.54	26.90	1.045	1.059
R	3.94	4.42	0.155	0.167
S	4.55	4.85	0.179	0.191
T	24.59	25.25	0.968	0.994
U	-0.05	0.10	-0.002	0.004
V	3.20	5.50	0.126	0.217
W	19.81	21.08	0.780	0.830
Z	2.50	2.70	0.098	0.106





SiC Diode (per leg)




Fig. 1 Typ. forward characteristics




Fig. 2 Typ. reverse characteristics




Fig. 3 Typ. current derating




Fig. 4 Power derating




Fig. 5 Typ. recovery charge vs. reverse voltage




Fig. 6 Typ. junction capacitance vs. reverse Voltage



SiC Diode (per leg)




Fig. 7 Typ. transient thermal impedance