



RESISTANCE @ +25°C = 2,252 Ω NOMINAL  
 ACCURACY (0 TO +70°C) = ± 0.10°C  
 RESISTANCE/TEMPERATURE CURVE = "J"  
 BETA "β" (0 TO +50°C) = 3,892°K NOMINAL  
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL  
 MAXIMUM TEMPERATURE RATING = +105°C

MAXIMUM TEMPERATURE FOR BEST LONG TERM STABILITY = +75°C

\*\*\* ROHS COMPLIANT

SEE MANUFACTURING SPECIFICATION (LAYER 1)

NONE	RELEASE TO PRODUCTION	09/30/10	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	© COPYRIGHT <b>U.S. SENSOR CORP.</b> 714-639-1000 www.ussensor.com <b>NTC THERMISTOR PROBE</b> P/N <b>USP11493</b>
DRAWN BY	DAN DANKERT	
DATE	09/30/10	
REV	NONE	
LAYER	0 OF 2	