



S8X5ECs EV Series

0.5 A Sensitive SCRs

HF RoHS

Pinout Diagram

TO-92



A: Anode; **K:** Cathode; **G:** Gate

Description

The S8X5ECs series offers a high static dv/dt with a low turn off (t_q) time. It is specifically designed for Ground Fault Circuit Interrupter (GFCI), Arc-Fault Circuit Interrupter (AFCI), Residual Current Device (RCD), and Residual Current Circuit Breaker with Overload Protection (RCBO) applications. All SCR junctions are glass-passivated to ensure long term reliability and parametric stability.

Features

- RoHS compliant and halogen-free
- Through-hole package
- Blocking voltage (V_{DRM} / V_{RRM}) capability up to 800 V
- Surge current capability < 20 A
- Sensitive gate for direct microprocessor interface
- High dv/dt noise immunity
- Improved turn-off time (t_q)
- Non-repetitive direct surge peak off-state voltage (V_{DSM}) up to 1150 V
- Non-repetitive reverse surge peak off-state voltage (V_{RSM}) up to 900 V

Applications

- Ground Fault Circuit Interrupter (GFCI) applications
- Arc-Fault Circuit Interrupter (AFCI) applications
- Residual Current Device (RCD) applications
- Residual Current Circuit Breaker with Overload Protection (RCBO) applications

Product Summary

| Characteristic | Value | Unit |
|----------------------------|----------|---------|
| $I_{T(RMS)}$ | 0.5 | A |
| V_{DRM} / V_{RRM} | 800 | V |
| $V_{DSM} (t_p = 50 \mu s)$ | 1150 | V |
| $V_{RSM} (t_p = 50 \mu s)$ | 900 | V |
| I_{GT} | 5 to 450 | μA |

Maximum Ratings

| Symbol | Characteristics | Conditions | | Value | Units | |
|--------------|--|-------------------------------|------------------------------|---------------------------------------|------------------------|---|
| $I_{T(RMS)}$ | On-state RMS Current | Full sine wave | $T_C = 85^\circ\text{C}$ | 0.5 | A | |
| $I_{T(AV)}$ | Average On-state Current | $T_C = 85^\circ\text{C}$ | | 0.3 | A | |
| I_{TSM} | Non-repetitive Surge Peak On-state Current | Half-sine wave | $f = 50\text{ Hz}$ | T_{vj} initial = 25°C | 10 | A |
| | | | $f = 60\text{ Hz}$ | | 12 | |
| I^2t | I^2t Value for Fusing | $t_p = 10\text{ ms}$ | $f = 50\text{ Hz}$ | 0.5 | A^2s | |
| di/dt | Critical Rate of Rise of On-state Current | $I_G = 10\text{ mA}$ | $T_{vj} = 125^\circ\text{C}$ | 80 | $\text{A}/\mu\text{s}$ | |
| I_{GM} | Peak Gate Current | $t_p = 20\text{ }\mu\text{s}$ | $T_{vj} = 125^\circ\text{C}$ | 0.5 | A | |
| $P_{G(AV)}$ | Average Gate Power Dissipation | $T_{vj} = 125^\circ\text{C}$ | | 0.2 | W | |
| T_{stg} | Storage Temperature Range | - | | -40 to 150 | $^\circ\text{C}$ | |
| T_{vj} | Virtual Junction Temperature Range | - | | -40 to 125 | $^\circ\text{C}$ | |

Electrical Characteristics ($T_{vj} = 25^\circ\text{C}$, unless otherwise specified)

| Symbol | Characteristics | Conditions | S8X5ECS | | | S8X5ECS2 | | | Units |
|----------------|--|---|---------|------|------|----------|------|------|------------------------|
| | | | Min. | Typ. | Max. | Min. | Typ. | Max. | |
| I_{GT} | DC Gate Trigger Current | $V_D = 6\text{ V}, R_L = 100\text{ }\Omega$ | 20 | - | - | 20 | - | - | μA |
| | | | - | - | 100 | - | - | 50 | |
| V_{GT} | DC Gate Trigger Voltage | $V_D = 6\text{ V}, R_L = 100\text{ }\Omega$ | - | - | 0.8 | - | - | 0.8 | V |
| V_{GRM} | Peak Reverse Gate Voltage | $I_{RG} = 10\text{ }\mu\text{A}$ | 8 | - | - | 8 | - | - | V |
| V_{GD} | Gate Non-trigger Voltage | $V_D = \frac{1}{2}V_{DRM}, R_{GK} = 1\text{ k}\Omega, T_{vj} = 125^\circ\text{C}$ | 0.2 | - | - | 0.2 | - | - | V |
| I_H | Holding Current | $R_{GK} = 1\text{ k}\Omega$, Initial current = 20 mA | - | - | 3 | - | - | 3 | mA |
| $dv/dt_{(cr)}$ | Critical Rate-of-rise of Off-stage Voltage | $T_{vj} = 125^\circ\text{C}, V_D = \frac{2}{3}V_{DRM}$, Exp. Waveform, $R_{GK} = 1\text{ k}\Omega$ | 40 | - | - | 40 | - | - | $\text{V}/\mu\text{s}$ |
| t_q | Turn-off Time | $I_T = 0.5\text{ A}$ | - | - | 35 | - | - | 35 | μs |
| t_{gt} | Turn-on Time | $I_G = 10\text{ mA}, P_W = 15\text{ }\mu\text{s}, I_T = 1.6\text{ A}_{pk}$ | - | 2.3 | - | - | 2.3 | - | μs |

Static Characteristics ($T_{vj} = 25^\circ\text{C}$, unless otherwise specified)

| Symbol | Characteristics | Conditions | Maximum Value | Units |
|-------------------|-----------------------------------|---|---------------|------------------|
| V_{TM} | Peak On-state Voltage | 0.5 A device, $I_{TM} = 4\text{ A}, t_p = 380\text{ }\mu\text{s}$ | 1.8 | V |
| V_{T0} | Threshold Voltage | - | 1.03 | V |
| r_T | Slope Resistance | - | 106 | $\text{m}\Omega$ |
| I_{DRM}/I_{RRM} | Repetitive Peak Off-state Current | $T_{vj} = 25^\circ\text{C}$ | 3 | μA |
| | | $T_{vj} = 125^\circ\text{C}$ | 500 | |

Thermal Characteristics

| Symbol | Characteristics | Conditions | Value | Units |
|---------------|---|------------------------------|-------|---------------------|
| $R_{th(j-c)}$ | Thermal Resistance, Junction to Case (AC) | $I_T = 0.8\text{ A}_{(RMS)}$ | 35 | K/W |
| $R_{th(j-a)}$ | Thermal Resistance, Junction to Ambient | $I_T = 0.8\text{ A}_{(RMS)}$ | 150 | K/W |

Note 1: 60 Hz AC resistive load condition, 100% conduction

Characteristic Curves

Fig. 1. Normalized DC Gate Trigger Current for all Quadrants vs. Junction Temperature




Fig. 2. Normalized DC Holding Current vs. Junction Temperature




Fig. 3. Normalized DC Gate Trigger Voltage vs. Junction Temperature




Fig. 4. Typical On-state Current vs. On-state Voltage




Fig. 5. Typical Power Dissipation vs. RMS On-state Current




Fig. 6. Maximum Allowable Case Temperature vs. On-state Current





Fig. 7. Surge Peak On-state Current vs. Number of Cycles




Notes:

1. Gate control may be lost during and immediately following surge current interval.
2. Overload may not be repeated until junction temperature has returned to steady-state rated value.

Soldering Parameters

| Characteristic | | Value |
|---|----------------------------------|-------------------------|
| Reflow Condition | | Pb – Free assembly |
| Pre-heat | Temperature Min ($T_{s(min)}$) | 150°C |
| | Temperature Max ($T_{s(max)}$) | 200°C |
| | Time (min to max) (t_s) | 60 – 180 secs |
| Average ramp up rate (Liquidus Temp)(T_L) to peak | | 5°C/second max |
| $T_{s(max)}$ to T_L - Ramp-up Rate | | 5°C/second max |
| Reflow | Temperature (T_L) (Liquidus) | 217°C |
| | Time (t_L) | 60 – 150 seconds |
| Peak Temperature (T_p) | | 260 ^{+0/-5} °C |
| Time within 5°C of actual peak Temperature (t_p) | | 20 – 40 seconds |
| Ramp-down Rate | | 5°C/second max |
| Time 25°C to peak Temperature (T_p) | | 8 minutes max |
| Do Not Exceed | | 280°C |



Environmental Specifications

| Test | Specifications and Conditions |
|---------------------------|---|
| AC Blocking | MIL-STD-750, M-1040, Cond A Applied Peak AC voltage @ 125 °C for 1008 hours |
| Temperature Cycling | MIL-STD-750, M-1051, 1000 cycles; -55 °C to +150 °C; 15-min dwell-time |
| Temperature/Humidity | EIA / JEDEC, JESD22-A101, 1008 hours; 320 V - DC: 85 °C; 85 % relative humidity |
| UHASt | JESD22-A118, 96 hours, 130 °C, 85 %RH |
| High-temperature Storage | MIL-STD-750, M-1031, 1008 hours; 150 °C |
| Low-temperature Storage | 1008 hours; -40 °C |
| Resistance to Solder Heat | MIL-STD-750: Method 2031 |
| Solderability | ANSI/J-STD-002: category 3, Test A |
| Lead Bend | MIL-STD-750, M-2036 Cond E |

Physical Specifications

| Characteristic | Value |
|-----------------|--|
| Terminal Finish | 100% Matte Tin-plated |
| Body Material | UL Recognized compound meeting flammability rating V-0 |
| Lead Material | Copper Alloy |



Design Considerations

Careful selection of the correct component for the application's operating parameters and environment will go a long way toward extending the operating life of the Thyristor. Good design practice should limit the maximum continuous current through the main terminals to 75% of the component rating. Other ways to ensure long life for a power discrete semiconductor are proper heat sinking and selection of voltage ratings for worst case conditions. Overheating, overvoltage (including dv/dt), and surge currents are the main killers of semiconductors. Correct mounting, soldering, and forming of the leads also help protect against component damage.

Packing Options

| Part Number | Marking | Weight | Packing Mode | Base Quantity |
|-------------|----------|---------|--------------|---------------|
| S8X5ECS | S8X5ECS | 0.217 g | Bulk | 2500 |
| S8X5ECSR | S8X5ECS | 0.217 g | Tape & Reel | 2000 |
| S8X5ECSAP | S8X5ECS | 0.217 g | Ammo Pack | 2000 |
| S8X5ECS2 | S8X5ECS2 | 0.217 g | Bulk | 2500 |
| S8X5ECS2RP | S8X5ECS2 | 0.217 g | Tape & Reel | 2000 |
| S8X5ECS2AP | S8X5ECS2 | 0.217 g | Ammo Pack | 2000 |


Part Numbering and Marking



Line1 = Littelfuse Part Number
Y = Last Digit of Calendar Year
M = Letter Month Code (A-L for Jan-Dec)
L = Location Code
DD = Calendar Date

TO-92


Package Dimensions TO-92



| Symbol | Millimeters | | Inches | |
|--------|-------------|-------|--------|-------|
| | Min. | Max. | Min. | Max. |
| A | 4.450 | 5.200 | 0.175 | 0.205 |
| B | 4.320 | 5.330 | 0.170 | 0.210 |
| C | 12.70 | – | 0.500 | – |
| D | 3.430 | – | 0.135 | – |
| E | 3.180 | 4.190 | 0.125 | 0.165 |
| F | 2.040 | 2.660 | 0.080 | 0.105 |
| G | 0.407 | 0.533 | 0.016 | 0.021 |
| H | 1.150 | 1.390 | 0.045 | 0.055 |
| I | 2.420 | 2.660 | 0.095 | 0.105 |
| J | 0.380 | 0.500 | 0.015 | 0.020 |


TO-92 (3-lead) Reel Pack (RP) Radial Leaded Specifications

Meets all EIA-468-C Standards



TO-92 (3-lead) Ammo Pack (AP) Radial Leaded Specifications

Meets all EIA-468-C Standards



Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.



Part of:

