


SP11xx Series Discrete Unidirectional TVS Diode



Description

Avalanche breakdown diodes fabricated in a proprietary silicon avalanche technology protect each I/O pin to provide a high level of protection for electronic equipment that may experience destructive electrostatic discharges (ESD). These robust diodes can safely absorb repetitive ESD strikes at $\pm 30\text{kV}$ (contact and air discharge, IEC 61000-4-2) without performance degradation. Additionally, each diode can safely dissipate 80A (SP1105S) of 8/20 μs surge current (IEC 61000-4-5 2nd edition) with very low clamping voltages.

Pinout and Functional Block Diagram



Features

- ESD, IEC 61000-4-2, $\pm 30\text{kV}$ contact, $\pm 30\text{kV}$ air
- EFT, IEC 61000-4-4, 40A (5/50ns)
- Lightning, IEC 61000-4-5 2nd edition, 80A ($t_p=8/20\mu\text{s}$, SP1105S)
- Low clamping voltage
- Low leakage current
- Moisture Sensitivity Level(MSL -1)
- Lead free and RoHS compliant
- AEC-Q101 qualified

Applications

- Switches / Buttons
- Test Equipment / Instrumentation
- Point-of-Sale Terminals
- Medical Equipment
- Notebooks / Desktops / Servers
- Computer Peripherals
- Automotive Electronics

Life Support Note:

Not Intended for Use in Life Support or Life Saving Applications

The products shown herein are not designed for use in life sustaining or life saving applications unless otherwise expressly indicated.

Absolute Maximum Ratings

Symbol	Parameter	Value	Units
T_{OP}	Operating Temperature	-40 to 125	°C
T_{STOR}	Storage Temperature	-55 to 150	°C

CAUTION: Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the component. This is a stress only rating and operation of the component at these or any other conditions above those indicated in the operational sections of this specification is not implied.

SP1105 Electrical Characteristics ($T_{OP}=25^{\circ}C$)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Units
Reverse Standoff Voltage	V_{RWM}	$I_R \leq 1\mu A$	-	-	5.0	V
Reverse Voltage Drop	V_R	$I_R = 1mA$	6.0	-	-	V
Leakage Current	I_{LEAK}	$V_R = 5V$	-	-	1.0	μA
Clamp Voltage ¹	V_C	$I_{PP} = 1A, t_p = 8/20\mu s, Fwd$	-	7.3	-	V
		$I_{PP} = 70A, t_p = 8/20\mu s, Fwd$	-	10.9	-	V
Dynamic Resistance ²	R_{DYN}	TLP, $t_p = 100ns, I/O$ to GND	-	0.05	-	Ω
Peak Pulse Current	I_{PP}	$t_p = 8/20\mu s$	-	-	70	A
ESD Withstand Voltage ¹	V_{ESD}	IEC 61000-4-2 (Contact Discharge)	± 30	-	-	kV
		IEC 61000-4-2 (Air Discharge)	± 30	-	-	kV
Diode Capacitance ¹	C_D	Reverse Bias=0V, f=1MHz	-	630	-	pF

SP1105S Electrical Characteristics ($T_{OP}=25^{\circ}C$)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Units
Reverse Standoff Voltage	V_{RWM}	$I_R \leq 1\mu A$	-	-	5.0	V
Reverse Voltage Drop	V_R	$I_R = 1mA$	6.0	-	7.5	V
Leakage Current	I_{LEAK}	$V_R = 5V$	-	-	1.0	μA
Clamp Voltage ¹	V_C	$I_{PP} = 40A, t_p = 8/20\mu s, Fwd$	-	8.3	-	V
		$I_{PP} = 80A, t_p = 8/20\mu s, Fwd$	-	9.2	-	V
Dynamic Resistance ²	R_{DYN}	TLP, $t_p = 100ns, I/O$ to GND	-	0.05	-	Ω
Peak Pulse Current	I_{PP}	$t_p = 8/20\mu s$	-	-	80	A
ESD Withstand Voltage ¹	V_{ESD}	IEC 61000-4-2 (Contact Discharge)	± 30	-	-	kV
		IEC 61000-4-2 (Air Discharge)	± 30	-	-	kV
Diode Capacitance ¹	C_D	Reverse Bias=0V, f=1MHz	-	630	-	pF

SP1112 Electrical Characteristics ($T_{OP}=25^{\circ}C$)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Units
Reverse Standoff Voltage	V_{RWM}	$I_R \leq 1\mu A$	-	-	12.0	V
Reverse Voltage Drop	V_R	$I_R = 1mA$	13.3	-	-	V
Leakage Current	I_{LEAK}	$V_R = 12V$	-	-	1.0	μA
Clamp Voltage ¹	V_C	$I_{PP} = 1A, t_p = 8/20\mu s, Fwd$	-	15.2	-	V
		$I_{PP} = 40A, t_p = 8/20\mu s, Fwd$	-	26.5	-	V
Dynamic Resistance ²	R_{DYN}	TLP, $t_p = 100ns, I/O$ to GND	-	0.05	-	Ω
Peak Pulse Current	I_{PP}	$t_p = 8/20\mu s$	-	-	40.0	A
ESD Withstand Voltage ¹	V_{ESD}	IEC 61000-4-2 (Contact Discharge)	± 30	-	-	kV
		IEC 61000-4-2 (Air Discharge)	± 30	-	-	kV
Diode Capacitance ¹	C_{D-GND}	Reverse Bias=0V, f=1MHz	-	230	-	pF

SP1115 Electrical Characteristics (T_{OP}=25°C)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Units
Reverse Standoff Voltage	V _{RWM}	I _R ≤ 1 μA	-	-	15.0	V
Reverse Voltage Drop	V _R	I _R = 1 mA	16.7	-	-	V
Leakage Current	I _{LEAK}	V _R = 15V	-	-	1.0	μA
Clamp Voltage ¹	V _C	I _{pp} = 1A, t _p = 8/20 μs, Fwd	-	19.3	-	V
		I _{pp} = 30A, t _p = 8/20 μs, Fwd	-	30.2	-	V
Dynamic Resistance ²	R _{DYN}	TLP, t _p = 100ns, I/O to GND	-	0.05	-	Ω
Peak Pulse Current	I _{pp}	t _p = 8/20 μs	-	-	30.0	A
ESD Withstand Voltage ¹	V _{ESD}	IEC 61000-4-2 (Contact Discharge)	±30	-	-	kV
		IEC 61000-4-2 (Air Discharge)	±30	-	-	kV
Diode Capacitance ¹	C _{I/O-GND}	Reverse Bias=0V, f=1 MHz	-	180	-	pF


SP1124 Electrical Characteristics (T_{OP}=25°C)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Units
Reverse Standoff Voltage	V _{RWM}	I _R ≤ 1 μA	-	-	24.0	V
Reverse Voltage Drop	V _R	I _R = 1 mA	26.7	-	-	V
Leakage Current	I _{LEAK}	V _R = 24V	-	-	1.0	μA
Clamp Voltage ¹	V _C	I _{pp} = 1A, t _p = 8/20 μs, Fwd	-	29.8	-	V
		I _{pp} = 20A, t _p = 8/20 μs, Fwd	-	44.7	-	V
Dynamic Resistance ²	R _{DYN}	TLP, t _p = 100ns, I/O to GND	-	0.1	-	Ω
Peak Pulse Current	I _{pp}	t _p = 8/20 μs	-	-	20.0	A
ESD Withstand Voltage ¹	V _{ESD}	IEC 61000-4-2 (Contact Discharge)	±30	-	-	kV
		IEC 61000-4-2 (Air Discharge)	±30	-	-	kV
Diode Capacitance ¹	C _{I/O-GND}	Reverse Bias=0V, f=1 MHz	-	130	-	pF


Note:

- Parameter is guaranteed by design and/or component characterization.
- Transmission Line Pulse (TLP) with 100ns width, 2ns rise time, and average window t1=70ns to t2= 90ns


8/20µs Pulse Waveform




Transmission Line Pulsing (TLP) Plot




SP1105, SP1105S Clamping voltage vs. I_{pp} for 8/20µs waveshape




SP1112, SP1115, SP1124 Clamping voltage vs. I_{pp} for 8/20µs waveshape



Capacitance vs. Bias




SP1105 IEC 61000 -4-2 +8 kV Contact ESD Clamping Voltage



SP1105 IEC 61000 -4-2 -8 kV Contact ESD Clamping Voltage




SP1105S IEC 61000 -4-2 +8 kV Contact ESD Clamping Voltage



SP1105S IEC 61000 -4-2 -8 kV Contact ESD Clamping Voltage




SP1112 IEC 61000 -4-2 +8 kV Contact ESD Clamping Voltage



SP1112 IEC 61000 -4-2 -8 kV Contact ESD Clamping Voltage




SP1115 IEC 61000 -4-2 +8 kV Contact ESD Clamping Voltage




SP1115 IEC 61000 -4-2 -8 kV Contact ESD Clamping Voltage



SP1124 IEC 61000 -4-2 +8 kV Contact ESD Clamping Voltage




SP1124 IEC 61000 -4-2 -8 kV Contact ESD Clamping Voltage




Soldering Parameters

Reflow Condition		Pb – Free assembly
Pre Heat	- Temperature Min ($T_{s(min)}$)	150°C
	- Temperature Max ($T_{s(max)}$)	200°C
	- Time (min to max) (t_s)	60 – 180 secs
Average ramp up rate (Liquidus) Temp (T_L) to peak		3°C/second max
$T_{s(max)}$ to T_L - Ramp-up Rate		3°C/second max
Reflow	- Temperature (T_L) (Liquidus)	217°C
	- Temperature (t_L)	60 – 150 seconds
Peak Temperature (T_p)		260 ^{+0/5} °C
Time within 5°C of actual peak Temperature (t_p)		20 – 40 seconds
Ramp-down Rate		6°C/second max
Time 25°C to peak Temperature (T_p)		8 minutes Max.
Do not exceed		260°C




Part Marking System



Part code :
AA = SP1105-01UTG
AB = SP1112-01UTG
AC = SP1115-01UTG
AD = SP1124-01UTG
AE = SP1105S-01UTG


Part Numbering System



Ordering Information


Part Number	Package	Marking	Min. Order Qty.
SP1105-01UTG	1.6x1.0mm DFN	AAKx	3000
SP1112-01UTG	1.6x1.0mm DFN	ABKx	3000
SP1115-01UTG	1.6x1.0mm DFN	ACKx	3000
SP1124-01UTG	1.6x1.0mm DFN	ADKx	3000
SP1105S-01UTG	1.6x1.0mm DFN	AEKx	3000

Package Dimensions



Symbol	1.6x1.0mm DFN		
	Millimeters		
	Min	Nor	Max
A	0.45	0.50	0.55
A1	-	0.02	0.05
D	1.55	1.60	1.65
E	0.95	1.00	1.05
b	0.75	0.80	0.85
L	0.35	0.40	0.45
e	1.10 BSC		
h	0.15	0.20	0.25

Embossed Carrier Tape & Reel Specification



Symbol	Millimeters
A0	1.14 +/- 0.03
B0	1.75 +/- 0.03
K0	0.67 +/- 0.05
F	3.50 +/- 0.05
P1	2.00 +/- 0.10
W	8.00 +/- 0.10

Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.