





PART NUMBER	"A"	"B"	"C"	"D"	LEAD "A" COLOR	LEAD "B" COLOR	LEAD "A" SIZE	LEAD "B" SIZE	LEAD "A" STRIP	LEAD "B" STRIP	INSULATION TYPE
OFHMO003ZXJV-F2	450±5 [17.72±0.2]	450±5 [17.72±0.2]	5.5±2 [0.22±0.08]	5.5±2 [0.22±0.08]	BLACK	BLACK	18 AWG	18 AWG	PARTIAL	PARTIAL	TXL

LTR	DATE	REVISION	CHK	APD
A	25/Sep/18	519894GCC - NEW RELEASE	FYUE	



IN-LINE FUSEHOLDER SHOWN WITH 2A MINI FUSE INSTALLED

- NOTES:
- HOLDER MATERIAL: BLACK TPV
  - CONTACTS: C194 COPPER ALLOY: TIN-PLATED
  - WIRE: STRANDED COPPER, 125°C RATED, 18AWG TXL WIRE
  - CRIMP: MUST MEET SAE/USCAR 21 STANDARD
  - FUSE RATING: 2A, 32Vdc
  - FUSEHOLDERS SHOULD NOT BE PLACED UNDER TENSION IN FINAL APPLICATION
  - MAX TEMPERATURE 125°C
  - THE HOLDER IS SHIPPED WITH COVER CLOSED

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS.  
DIMENSIONS IN BRACKETS [ ] ARE INCHES

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

⊙	DENOTES CRITICAL CHARACTERISTICS.
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

COPIES TO	MATL SPEC	SEE NOTES
1 9 18	FINISH	SEE NOTES
2 10 19	DRW	FYUE
3 12 20	DATE	25/Sep/18
4 13 21	SCALE	1:1
5 14 23	CHK	DATE
6 15 33	DATE	SUPER DR
7 16 43	APPD	DATE
8 17 53	FINISH GOOD WT	GRAMS/PIECE

TOLERANCE UNLESS OTHERWISE SPECIFIED  
ONE PLACE DEC +/- .3      THREE PLACE DEC +/- .100  
TWO PLACE DEC +/- .15      ANGULAR +/- 1°

3RD ANGLE PROJECTION	TITLE	MINI IN-LINE FUSEHOLDER WITH 2A FUSE
Littelfuse	REVISION	A
DES PLAINES, ILLINOIS 60016	DRWG. NO.	OL-OFHMO003ZXJV-F2
	OUTLINE	

METRIC

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED