


PART NUMBER	"A"	"B"	"C"	"D"	LEAD "A" COLOR	LEAD "B" COLOR	WITH FUSE
OFHM0001ZXJA	150±5 [5.91±0.2]	150±5 [5.91±0.2]	NO END STRIP	NO END STRIP	RED	RED	3A
OFHM0001ZXJB	150±5 [5.91±0.2]	150±5 [5.91±0.2]	NO END STRIP	NO END STRIP	BLUE	BLUE	3A

LTR	DATE	REVISION	CHK	APD
A	5/AUG/16	516235ECC-NEW RELEASE FYUE		



IN-LINE FUSEHOLDER SHOWN WITH MINI FUSE INSTALLED (NOT INCLUDED)

- NOTES:
- HOLDER MATERIAL: BLACK TPV
  - CONTACTS: COPPER ALLOY: TIN-PLATED
  - WIRE: 20 AWG UL1015 WIRE
  - CRIMP: MUST MEET SAE/USCAR 21 STANDARD
  - RATING: 3A, 32Vdc
  - FUSEHOLDERS SHOULD NOT BE PLACED UNDER TENSION IN FINAL APPLICATION
  - MAX TEMPERATURE 105°C

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [ ] ARE INCHES			
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.			
⊙	DENOTES CRITICAL CHARACTERISTICS.		
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE		
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS		
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE		
COPIES TO	MATL SPEC SEE NOTES		
1 9 18	FINISH SEE NOTES		
2 10 19			
3 12 20			
4 13 21	DRW	DATE	SCALE
5 14 23	FYUE	05/AUG/16	1:1
6 15 33	CHK	DATE	SUPER DR
7 16 43	APPD	DATE	FINSH GOOD WT
8 17 53			GRAMS/PIECE
TOLERANCE UNLESS OTHERWISE SPECIFIED			
ONE PLACE DEC +/- .3		THREE PLACE DEC +/- .100	
TWO PLACE DEC +/- .15		ANGULAR +/- 1°	
3RD ANGLE PROJECTION	TITLE	MINI IN-LINE FUSEHOLDER	
Littelfuse		REVISION	DRWG. NO. OUTLINE
DES PLAINES, ILLINOIS 60016		A	OFHM0004ZXJ

METRIC

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED