



METRIC
COMPONENT

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
◎	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			

LTR	DATE	REVISION	CHK	APD
A	06/21/16	516036GCA-INITIAL RELEASE FYUE		

COPIES TO	MATL SPEC		
1 9 18	2.0mm MS PLATE		
2 10 19	FINISH		
3 12 20	ZINC CHROMATE PLATED (t = 3-8 microns)		
4 13 21	DATE	21/Jun/16	SCALE
5 14 23	FYUE		1:1
6 15 33	CHK		SUPER DR
7 16 43	APPD		FINISH GOOD WT
8 17 53	GRAMS/PIECE		

TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)	UP TO 0.5	UP TO 3	UP TO 6	UP TO 30	UP TO 120	UP TO 400
DIMENSION	±0.1	±0.1	±0.2	±0.3	±0.5	±0.5
TOLERANCE						

3RD ANGLE PROJECTION	TITLE	METAL BRACKET (for HWB18)	
----------------------	-------	------------------------------	--

REVISION	DRWG. NO.	OUTLINE
A	868-066	

Littelfuse
LIPA CITY, BATANGAS, PHILIPPINES