



- NOTES:  
 1. MATERIAL: COPPER C1100, TIN PLATED  
 2. UNLESS OTHERWISE NOTED, BURR SHALL NOT EXCEED 10% OF THE RAW MATERIAL THICKNESS AT ANY LOCATION  
 3. PART TO BE CLEAN, DEGREASED, FREE OF CONTAMINATION

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [ ] ARE INCHES

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

⊙ DENOTES CRITICAL CHARACTERISTICS.

CPK DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE

ST DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS

CP DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				

LTR	DATE	REVISION	CHK	APD
A	06/26/13	50B674ERA-RELEASE FYUE		
B	07/10/13	50B881ECA-THICKNESS 2.3 WAS 2.0 FYUE		

COPIES TO	MATERIAL SPEC			
1 9 18	SEE NOTE			
2 10 19	FINISH			
3 12 20	SEE NOTE			
4 13 21	DATE	06/26/13	SCALE	2:1
5 14 23	DATE			SUPER DR
6 15 33	DATE			FINISH GOOD WT
7 16 43	DATE			GRAMS/PIECE
8 17 53	TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)			
DIMENSION	0.5 - 3	3 - 6	6 - 30	30 - 120
TOLERANCE	+0.05	+0.05	+0.1	+0.15
3RD ANGLE PROJECTION				
TITLE 3 POSITION BUS BAR - FLEX MIDI HOLDER				
CHICAGO, USA 773-628-1000				REVISION B DRWG. NO. OL-882-267-003