



NOTES:  
 1. MATERIAL: COPPER C1100, TIN PLATED  
 2. UNLESS OTHERWISE NOTED, BURR SHALL NOT EXCEED 10% OF THE RAW MATERIAL THICKNESS AT ANY LOCATION  
 3. PART TO BE CLEAN, DEGREASED, FREE OF CONTAMINATION

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [ ] ARE INCHES  
 UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

⊙ DENOTES CRITICAL CHARACTERISTICS.  
 CPK DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE  
 Ⓢ DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS  
 CP DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				

LTR	DATE	REVISION	CHK	APD	COPIES TO	MATL SPEC	SEE NOTE	
						FINISH	SEE NOTE	
A	06/26/13	50B674ERA-RELEASE	FYUE		1 9 18	DRW	DATE 06/26/13	SCALE 2:1
B	07/10/13	50B881ECA-THICKNESS 2.3 WAS 2.0	FYUE		2 10 19	CHK	DATE	SUPER DR
					3 12 20	APPD	DATE	FINISH GOOD WT
					4 13 21	TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)		
					5 14 23	DIMENSION 0.5 - 3 3 - 6 6 - 30 30 - 120 120 - 400		
					6 15 33	TOLERANCE +0.05 ±0.05 ±0.1 ±0.15 ±0.2		
					7 16 43	3RD ANGLE PROJECTION		
					8 17 53	TITLE 4 POSITION BUS BAR - FLEX MIDI HOLDER		
						REVISION B		
						DRWG. NO. OL-882-267-004		
						Littelfuse CHICAGO, USA 773-628-1000		