

8 7 6 5 4 3 2 1

THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

ITEM	DESCRIPTION	PART NUMBER
A	2-POSITION	882-869-2
B	3-POSITION	882-869-3
C	4-POSITION	882-869-4
D	5-POSITION	882-869-5
E	6-POSITION	882-869-6
F	7-POSITION	882-869-7

REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	PCO #5300103. INITIAL RELEASE. DSILVA	10/4/2022	L.ARGIL

(7X) Ø 10.5 THRU

23.8

11.9

13.5

32 TYP

59 FOR 2-POSITION ONLY

91 FOR 3-POSITION ONLY

123 FOR 4-POSITION ONLY

155 FOR 5-POSITION ONLY

187 FOR 6-POSITION ONLY

219 FOR 7-POSITION ONLY

SCALE 1:2

NO.	COMPONENT NO.	COMPONENT NAME	QTY	U

TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)

.5 to 3	>3 to 6	>6 to 30	>30 to 120	>120 to 400	ANGLE
±0.05	±0.05	±0.10	±0.15	±0.20	NONE

DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.

PER CHI-NPD20-0008 PROCEDURE

- FIT/ FUNCTION CRITICAL CHARACTERISTICS
- <S> SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL
- CPK DENOTES CPK DIMENSIONS MINIMUM CPK VALUE
- (ST) DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
- CP DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

NAME	DATE	 Littelfuse Expertise Applied Answers Delivered	TITLE
DRAWN DSILVA	9/12/2022		
CHECKED -	-	SIZE B DWG. NO. OL-882-869-0 OUTLINE	REV. A
DO NOT SCALE DRAWING		SCALE 1:1	SHEET 1 OF 1

NOTES:
1. MATERIAL: COPPER, TIN PLATED.

8 7 6 5 4 3 2 1