



NOTES:

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY
2. MATERIAL: BODY -- MAPEX UL94 -V0, BLACK
M8 x 1.25 STUD -- SAE1215/DIN 9SMn28/11SMn30 STEEL, ZINC PLATED
3. MAXIMUM MOUNTING TORQUE FOR M4 MOUNTING HOLES 10 N*M, 7.4 LBF*FT
4. MAXIMUM TORQUE FOR M8 STUD 8.9-13.3 LBF*FT, 12-18 N*m

METRIC
ASSEMBLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS.
DIMENSIONS IN BRACKETS [] ARE INCHES

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

⊙	DENOTES CRITICAL CHARACTERISTICS.
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

2	STUD	1	EA
1	BODY	1	EA
NO	COMPONENT NO	DESCRIPTION	QTY/M

BILL OF MATERIAL

COPIES TO	MATERIAL SPEC		SEE NOTE 2	
1	9	18	FINISH	
2	10	19	SCALE	
3	12	20	DATE	03/21/12
4	13	21	PVN	SUPER DR
5	14	23	DATE	FINISH GOOD WT
6	15	33	DATE	GRAMS/PIECE
7	16	43	DATE	
8	17	53	DATE	

DIMENSION	0.5 - 3	UP TO OVER	3 - 6	UP TO OVER	6 - 30	UP TO OVER	30 - 120	UP TO OVER	120 - 400	
TOLERANCE	±0.1		±0.1		±0.2		±0.3		±0.5	
TOLERANCES UNLESS OTHERWISE SPECIFIED										
TITLE JUNCTION BLOCK										
NON-FEED-THRU										

REVISION	DRWG. NO.
B	OL-JBPT5N01ZXB

