



RESISTANCE @ +25°C = 100,000 Ω ± 10%
 RESISTANCE/TEMPERATURE CURVE = "R"
 BETA "β" (0 TO +50°C) = 4,140°K NOMINAL
 TEMPERATURE COEFFICIENT @ +25°C = -4.68%/°C NOMINAL
 DISSIPATION CONSTANT = 1 mW/°C NOMINAL
 THERMAL TIME CONSTANT = 5 SECONDS MAXIMUM
 MAXIMUM TEMPERATURE RATING = +220°C

| | | | |
|-----|-----------------|----------|-----|
| --- | ISO RELEASE | 08/22/03 | DD |
| REV | REVISION RECORD | DATE | APP |

| | |
|-------------------------|---|
| SCALE NONE | U.S. SENSOR CORP. © COPYRIGHT 714-639-1000 www.ussensor.com |
| DRAWN BY DAN DANKERT | |
| DATE 05/22/02 | NTC THERMISTOR |
| REV NONE | P/N MM104R1K |
| LAYER 0 OF 1 | |