



RESISTANCE @ +25°C = 2,700 Ω ± 10%  
 RESISTANCE/TEMPERATURE CURVE = "J"  
 BETA "β" (0 TO +50°C) = 3,892°K NOMINAL  
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL  
 DISSIPATION CONSTANT = 3 mW/°C NOMINAL  
 THERMAL TIME CONSTANT = 8 SECONDS MAXIMUM  
 MAXIMUM TEMPERATURE RATING = +220°C

|      |                       |          |     |
|------|-----------------------|----------|-----|
| NONE | RELEASE TO PRODUCTION | 08/18/08 | DD  |
| REV  | REVISION RECORD       | DATE     | APP |

|                         |  |
|-------------------------|--|
| SCALE NONE              | © COPYRIGHT<br><b>U.S. SENSOR CORP.</b><br>www.ussensor.com sales@ussensor.com<br><b>NTC THERMISTOR</b><br><b>P/N SB272J1K</b> |
| DRAWN BY<br>DAN DANKERT |  |
| DATE 08/18/08           |  |
| REV. NONE               |  |
| LAYER 0 OF 1            |  |