



RESISTANCE @ +25°C = 50,000  $\Omega \pm 10\%$   
 RESISTANCE/TEMPERATURE CURVE = "J"  
 BETA " $\beta$ " (0 TO +50°C) = 3,892°K NOMINAL  
 TEMPERATURE COEFFICIENT @ +25C = -4.4%/°C NOMINAL  
 DISSIPATION CONSTANT = 2 mW/°C NOMINAL  
 THERMAL TIME CONSTANT = 8 SECONDS NOMINAL  
 MAXIMUM TEMPERATURE RATING = +220°C

REV	REVISION RECORD	DATE	APP
---	ISO RELEASE	12/09/03	DD
"A"	TAB WAS $0.019'' \pm 0.004''$ , LENGTH WAS $0.140'' \pm 0.010''$ & DIA WAS $0.065'' \pm 0.004''$	12/09/03	DD

SCALE NONE	U.S. SENSOR CORP. © COPYRIGHT 714-639-1000 www.ussensor.com
DRAWN BY DAN DANKERT	
DATE 11/03/95	NTC THERMISTOR
REV. "A"	P/N SM503J1K
LAYER 0 OF 2	