


LTR	DATE	REVISION	CHK	APD
A	04/24/15	511284GCA-NEW RELEASE FYUE		

NOTES:

1. MATERIALS:


HOUSING: BLACK PBT, 15% GLASS FIBER REINFORCED

TERMINAL: TIN PLATED COPPER ALLOY




3D VIEW
SCALE 2:1

3D VIEW
SCALE 2:1



MOUNTING HOLE SINGLE LAYOUT



MOUNTING HOLE ROW LAYOUT

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
⊙	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			
COPIES TO		MATL SPEC		
1 9 18		REFER TO NOTES		
2 10 19		FINISH		
3 12 20		REFER TO NOTES		
4 13 21		DRW	FYUE	DATE 04/24/15
5 14 23		CHK		SCALE 5:1
6 15 33		APPD		SUPER DR
7 16 43				FINSH GOOD WT
8 17 53				GRAMS/PIECE
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-MH)				
DIMENSION	0.5 - 3	UP TO 3	UP TO 6	UP TO 30
TOLERANCE	±0.1	±0.1	±0.2	±0.3
3RD ANGLE PROJECTION				
TITLE FL1 PCB MINI FUSE HOLDER				
Littelfuse				
CHICAGO, USA 773-628-1000				
REVISION		DRWG. NO.		OUTLINE
A		178.6764.0001		

METRIC
ASSEMBLY

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED (rev C)