

Ø30.9 ± 0.38
[Ø1.218 ± 0.015]

4.7 ± 0.15
[0.187 ± 0.006]

7.9 ± 0.25
[0.312 ± 0.010]

71.45 ± 1.60
[2.813 ± 0.063]

74.60 ± 1.60
[2.937 ± 0.063]

92.1 ± 1.60
[3.625 ± 0.063]

54.0
[2.125]

22.7 ± 0.89
[0.895 ± 0.035]

REVISION

REV	DATE	DESCRIPTION
A	7/6/23	526696GCP - RELEASE MRY

1	NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
---	----	--------------	-------------	-------	-----

BILL OF MATERIAL

<S> CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE

● DENOTES CRITICAL CHARACTERISTICS.

CPK DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE

ST DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.

CP DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.

A

MATL SPEC

FINISH

DRW
JMoler

DATE
6/22/2023

SCALE
NTS

FINISH GOOD WT
GRAMS/PIECE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994

3RD ANGLE
PROJECTION



TITLE

L50S 125-200A OUTLINE

 **Littelfuse**[®]
CHICAGO, ILLINOIS 60631

REVISION

A

DRWG NO.

OL-L50S200

SHEET 1 OF 1