



LLC2 SERIES

Open Board Liquid Level Controls



Wiring Diagram



Description

The LLC2 Series is a dual-probe conductive liquid level control designed for OEM equipment and commercial appliance applications. Models are available for fill or drain operation. Transformer isolated 12VAC is provided at the probes to prevent electrolysis. A trickle current of less than 1mA determines the presence or absence of liquid between the probes and common. On adjustable units, the sensitivity adjustment allows accurate level sensing while ignoring foaming agents and floating debris. The LLC2 Series printed circuit board is conformal coated to resist moisture and corrosion.

Operation

Drain (Pump-Down Mode): When the liquid level rises and touches the high probe, the output relay energizes and remains energized until the liquid level falls below the low probe. The output relay then de-energizes and remains de-energized until the liquid again touches the high probe.

Fill (Pump-Up Mode): When the liquid level falls below the low probe, the output relay energizes and remains energized until the liquid level rises and touches the high probe. The output relay then de-energizes and remains de-energized until the liquid level again falls below the low probe.

Features & Benefits

FEATURES	BENEFITS
Isolated 12VAC probes	Prevents scale buildup on the probes
Open PCB design	Cost effective design for OEM equipment and commercial appliances
Conformally coated PCB	Protects against moisture and corrosion
Sensitivity adjustment	Provides accurate level sensing while ignoring foam or floating debris

Ordering Information

MODEL	INPUT VOLTAGE	OPERATION	TERMINATION	SENSE RESISTANCE
LLC24A2AN	120VAC	Drain	Terminal block	Adjustable to 100k Ω
LLC24A2F50N	120VAC	Drain	Terminal block	Fixed 50k Ω
LLC24B1AC	120VAC	Fill	0.25" Quick connect	Adjustable to 100k Ω
LLC24B1F26C	120VAC	Fill	0.25" Quick connect	Fixed 26k Ω
LLC24B2F50N	120VAC	Fill	Terminal block	Fixed 50k Ω
LLC26A1F25C	230VAC	Drain	0.25" Quick connect	Fixed 25k Ω

If you don't find the part you need, call us for a custom product 800-843-8848

Accessories



P1015-13 (AWG 10/12), **P1015-64** (AWG 14/16), **P1015-14** (AWG 18/22) **Female Quick Connect**
These 0.25 in. (6.35 mm) female terminals are constructed with an insulator barrel to provide strain relief.



P1015-18 Quick Connect to Screw Adapter
Screw adapter terminal designed for use with all modules with 0.25 in. (6.35 mm) male quick connect terminals.



PHST-38QTN Electrode
Designed for a maximum steam pressure of 240 PSI; 400° F. UL353 Recognized.



LLP-24 Threaded Probe (24")
Threaded stainless steel probe measuring 24" (61 cm) long. For use with PHST-38QTN liquid level control electrodes.

LLC2 SERIES

Specifications

Control

Type	Resistance sensing for high & low level detection of conductive liquids
Sense Voltage	12VAC at probe terminals
Sense Resistance	Fixed or adjustable to 100K Ω
Sense Resistance Tolerance	Adjustable: guaranteed range Fixed: $\pm 10\%$

Input

Voltage	24, 120, or 230VAC
Tolerance	
24VAC	-15% - 20%
120 & 230VAC	-20% - 10%
AC Line Frequency	50/60 Hz

Output

Type	Electromechanical relay
Form	Isolated, SPDT
Rating	10A resistive @ 120/240VAC & 28VDC; 1/3 hp @ 120/240VAC
Life	Mechanical - 1×10^7 ; Electrical - 1×10^6

Protection

Isolation Voltage	$\geq 1500V$ RMS between input, output, & probe
--------------------------	---

Mechanical

Mounting	Surface mount with two or four #6 (M3.5 x 0.6) screws
Termination	0.25 in. (6.35 mm) duplex male quick connect terminals. Terminal blocks for up to #14 AWG 2.5 mm ² wire
Dimensions (Open Board)	H 101.6 mm (4.0"); W 76.2 mm (3.0"); D 50.8 mm (2.0")

Environmental

Operating/Storage Temperature	-20° to 55°C / -40° to 80°C
Coating	Printed circuit board is conformal coated to resist moisture and corrosion
Weight	≈ 9 oz (255 g)

Mounting Dimensions




DIAGRAM KEY	MODEL NUMBERS ENDING IN:	
	N	C
W	0.440" (11.176 mm)	0.250" (6.350 mm)
X	3.620" (91.948 mm)	3.500" (88.900 mm)
Y	2.120" (53.848 mm)	2.500" (63.500 mm)
Z	0.190" (4.826 mm)	0.250" (6.350 mm)