


| REV | DATE      | REVISION DESCRIPTION    |
|-----|-----------|-------------------------|
| A   | 6/13/2011 | 502552ERP - RELEASE MRY |



**SPECIFICATIONS:**

**VOLTAGE RATING:** 600V

**AMPERE RATING:** 400 AMPERES

**INTERRUPT RATING:** 200kA

**TERMINAL TYPE:** BOX LUG

**SUGGESTED TORQUE:** 31.1 N-m (275in-lb)

**WIRE RANGE:** 350kcmil-1/0 Cu/Al  
SOLID/STRANDED

**APPROVALS:** UL LISTED (FILE NO. E14721)  
CSA CERTIFIED (FILE NO. 007316\_0\_000)

|      |   |
|------|---|
| ●    | DENOTES CRITICAL CHARACTERISTICS.   |
| CPK  | DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE  |
| (ST) | DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS |
| CP   | DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.              |

|             |                |           |                            |
|-------------|----------------|-----------|----------------------------|
| MATL SPEC   | FINISH         |           |                            |
| DRW M. York | DATE 3/18/2011 | SCALE NTS | FINISH GOOD WT GRAMS/PIECE |

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [ ] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994

|                      |  |
|----------------------|--|
| 3RD ANGLE PROJECTION |  |
|----------------------|--|

|       |                         |
|-------|-------------------------|
| TITLE | LFJ60400 SERIES OUTLINE |
|-------|-------------------------|

|  |          |                    |              |
|--|----------|--------------------|--------------|
|  | REVISION | DRWG NO.           | SHEET 1 OF 1 |
|  | A        | OL-LFJ60400 Series |              |