


2

1



Mechanical Dimensions :

A	B	C	D	E
$0.126" \pm 0.012"$ (3.2004 $\pm$ 0.3048mm)	$0.063" \pm 0.008"$ (1.6002 to 0.2032 mm)	0.059" Max (1.4986 Max)	$0.022" \pm 0.014"$ (2X) (0.5588 $\pm$ 0.3556mm (2X))	Solder Plated Terminations Ends

Electrical Specifications :

Resistance (25 °C) Ω	Resistance Tolerance, $\pm\%$	Temp, Coefficient (%/ °C)	Beta(K)	Temp Rating(°C)	Power Rating(V)	Packaging
100 to 100000	1 to 10	3.31 to 4.4	2000~5000	-55~ +150	300~400	Tape & Reel

A	Initial Release	RKM	04/04/2023	
Rev	Description	By	Date	ECO NO
Revision History				
Reference Legacy No.		USPxxxx REV x		

Project Code	XXXXX			 Littelfuse®	
	Third Angle Projection				
Units	Inch(mm)			Division	IBU - Temperature Sensors
General Tolerances 0.X = ± 0.X 0.XX = ± 0.XX 0.XXX = ± 0.XXX				Title	End Banded NTC Thermistor Chips-1206
				Finished Product Part Number	NSLR
Drawn By	RKM			Internal No.	NSLR
					Rev A
Date	04/04/2023			Size	A
				Do Not Scale	
				Sheet	1 of 1

2

1