



NOTES :

1. FUSEHOLDER IS SPLASHED-WATERPROOF ACCORDING TO CLASS IP-64 AS DEFINED IN DIN 40050 BLATT 9 DATE FEB. 1975.

METRIC COMPONENT

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES				
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.				
◎	DENOTES CRITICAL CHARACTERISTICS.			
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE			
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS			
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE			

LTR	DATE	REVISION	CHK	APD
A	03/20/09	00636ER-RELEASE GMB		
B	06/23/11	502726ECA-REDRAWN BASED FROM AVAILABLE 3D MODEL. CORRECTED REFERENCE POSITION OF DIM 66.5mm. RLDJ		
C	7/15/11	502842ECA-UPDATE DRAWING BASED ON ACTUAL PART SUPPLIED TO MARKET. ADD RIB ON LATCH AREA AND CHAMFER ON MAXI BLADE LEG OPENING.		

COPIES TO	1	9	18
	2	10	19
	3	12	20
	4	13	21
	5	14	23
	6	15	33
	7	16	43
	8	17	53

MATL SPEC	PA66 GF 30%
FINISH	
DRW	RLDJ
CHK	DATE
APPD	DATE

TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-fH)	UP TO	OVER	UP TO	OVER	UP TO	OVER
DIMENSION	0.5 - 3	3 - 6	6 - 30	30 - 120	120 - 400	UP TO
TOLERANCE	±0.05	±0.05	±0.1	±0.15	±0.2	

3RD ANGLE PROJECTION	TITLE	SPLASH-PROOF
		MAXI FUSEHOLDER
	REVISION	DRWG. NO.
	C	OL-01520003U