







REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	520253GCC-NEW RELEASE DRAWING	23/May/19	




SECTION A-A



NOTES:

- MATERIALS:
BASE/COVER: PET WITH GF (UL-94V0)
BUS BAR: COPPER Sn PLATED
DUST COVER: SILICON RUBBER
STUD: STEEL Ni/Fe ALLOY PLATED
BOTTOM CAP: PA66
LATCH: POM
FLANGE NUT: STAINLESS STEEL
- MAX. MAIN INPUT: 400A
- OPERATING TEMPERATURE RANGE: -40°C TO 85°C
- M8 MOUNTING TORQUE: 12-15 Nm
- MAX. WIRE SIZE 105 sqmm OR AWG 4/0

9	873-723	COVER	1	EA
8	883-088	LATCH	2	EA
7	901-520	DUST COVER	7	EA
6	980003760	M8 NUT	7	EA
5	882-869-7	BUS BAR	1	EA
4	890009470	TETHER	1	EA
3	868-994	BASE	1	EA
2	908-067	M8 STUD	7	EA
1	883-097	BOTTOM CAP	2	EA
NO.	COMPONENT NO.	COMPONENT NAME	QTY/M	U/M

DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.		
	DENOTES PRODUCTS CRITICAL CHARACTERISTICS	
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE	
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS	
CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE	
TOLERANCES UNLESS OTHERWISE SPECIFIED		
ONE PLACE DECIMAL ± 0.5 THREE PLACES DECIMAL ± 0.100		
TWO PLACES DECIMAL ± 0.20 ANGULAR ± 2°		
NAME	DATE	 Littelfuse® Expertise Applied Answers Delivered
DRAWN	FRANK YUE 26/Dec/17	
CHECKED	-	
	-	
	-	
THIRD ANGLE PROJECTION		TITLE
		UNSEALED 6-WAY ZCASE FUSE BOX
SIZE	DWG. NO.	REV.
C	OL-0FHZ0007Z	A
DO NOT SCALE DRAWING		SHEET 1 OF 1