



CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED



METRIC  
COMPONENT

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS.  
DIMENSIONS IN BRACKETS [ ] ARE INCHES  
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

⊙ DENOTES CRITICAL CHARACTERISTICS.  
CPK DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE  
ST DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS  
CP DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				

LTR	DATE	REVISION	CHK	APD
A	03/20/09	006388R-RELEASE GMB		

COPIES TO	MATL SPEC
1 9 18	CLEAR POLYCARBONATE
2 10 19	(SEAL IS SILICON MVQ 40
3 12 20	±5 SHORE A)
4 13 21	FINISH
5 14 23	SCALE N/A
6 15 33	DATE 03/20/09
7 16 43	DATE SUPER DR
8 17 53	DATE FINISH GOOD WT

TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-TH1)	±0.05	±0.1	±0.15	±0.2
DIMENSION	0.5 - 3	3 - 6	6 - 30	30 - 120
TOLERANCE	±0.05	±0.05	±0.1	±0.15

PROJECTION  
TITLE COVER

REVISION DRWG. NO. 01520903U  
OUTLINE A

**LITTELFUSE**  
DES. PLATES, ILLINOIS 60116