



F FUJIX
32V 20A
153 MAX.

RECOMMENDED P.C.B. LAYOUT
(MOUNTING SIDE)

MATERIAL:
BODY-BLACK GLASS FILLED
THERMOPLASTIC (UL94V-0).
CLIP COPPER ALLOY, TIN PLATE FINISH

TOLERANCES:
TWO PLACE DEC ±.01
THREE PLACE DEC ±.005

METRIC
ASSEMBLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES.	
◀▶	UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.
●	CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE.
CPK	CRITICAL CHARACTERISTIC FOR PART FIT/FUNCTION.
ST	CPK DIMENSION. 1.67 MINIMUM CPK VALUE ON NEW TOOLING.
CP	STATISTICAL PROCESS CONTROL DIMENSION. THIS DIMENSION INDICATES PROCESS PERFORMANCE. DATA SHALL BE TRACKED AND ANALYZED AT PERIODIC TIMES, ACC. TO CONTROL PLAN.
Ⓞ	CP DIMENSION. 1.67 MINIMUM CP VALUE. MUST BE INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.
Ⓜ	CUSTOMER-DESIGNATED CHARACTERISTIC. REQUIREMENT FOR EACH SYMBOL TO BE DEFINED IN A CONVERSION TABLE.
Ⓐ	CLAMP DIMENSION. PARTS SHALL BE SECURED BEFORE TAKING DIMENSIONAL MEASUREMENTS. FIXTURING DATUMS & PROCEDURES TO BE DEFINED IN NOTES OR SEPARATE PROCESS DOCUMENTS.

DIMENSIONS & TOLERANCES ACC. TO ASME Y14.5-2009		MATERIAL SPEC	
3RD ANGLE PROJECTION		FINISH	
SCALE	DRW	OPR	CHK
TOLERANCES UNLESS OTHERWISE SPECIFIED			
LINEAR DIMENSIONS		ANGLES	
DIM	UP TO OVER	UP TO OVER	RADII
	.5 - .6	30 - 120	±0.5°
TOL	±0.1	±0.2	±0.2
TITLE			
MINIFUSE SINGLE VERTICAL MOUNT			
P.C.B. HOLDER			
LTR	DATE	REVISION	DRW
A	12/JAN/18	518732GCA-RELEASE	OPL
LITLITFUSE		REVISION DRWG. NO.	
CHICAGO, USA 773-628-1000		A OL-01530032Z	