



NOTES:

- 1) BASE: UL94V0, GLASS FILLED PA66, BLACK
M5 STUDS: ZINC-PLATED STEEL
COVER: THERMOPLASTIC ELASTOMER, BLACK
HEX NUTS: STEEL
LOCK WASHERS: STEEL
- 2) MAX FUSE RATING: 200A
- 3) M5 STUD TORQUE: 3-5.0 Nm MAX
MOUNTING TORQUE: WITH M4 BOLTS AND WASHERS: 5Nm MAX
- 4) TEMPERATURE RATING: -40°C TO 125°C

METRIC
ASSEMBLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS.
DIMENSIONS IN BRACKETS [] ARE INCHES
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

©	DENOTES CRITICAL CHARACTERISTICS.
CPK	DENOTES CPK DIMENSIONS. -MINIMUM CPK VALUE
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

4	SPLIT LOCK WASHER, M5	EA	2
3	HEX NUT, M5X.8	EA	2
2	COVER	EA	1
1	BASE	EA	1
NO COMPONENT NO	DESCRIPTION	QTY/M	U/M

BILL OF MATERIAL		MATERIAL SPEC	
SEE NOTES		SEE NOTES	
FINISH		SCALE 1:1	
DATE	10/18/12	DATE	10/18/12
CHK		DATE	
APPD		DATE	
FINISH GOOD WT		GRAMS/PIECE	
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-MK)		0.5 - 1.3 ^{0.00} 3 ^{0.00} 6 ^{0.00} 30 - 120 ^{0.05} 120 - 400 ^{0.10}	
DIMENSION		TOLERANCE	
TITLE		FLEX-MIDI FUSE HOLDER	
LITTLEFUSE		REVISION DRWG. NO.	
CHICAGO, USA 773-628-1000		B	
OL-04981038HXFC			
LTR	DATE	REVISION	CHK
B	10/18/12	RELEASE FOR PRODUCTION. PCA 50000006363, 10/18/12	PN