






DFK-CONTACTS
ART.NO.:376.1414.2225
INSIDE


COVER
ART.NO.:372.2133.0001


HOLDER
ART.NO.:371.6115.0002



LTR	DATE	REVISION	CHK	APD
A	15/Feb/16	515549GCA-NEW RELEASED FYUE		

3D VIEW
SCALE 2:1



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES						
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.						
	DENOTES CRITICAL CHARACTERISTICS.					
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE					
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS					
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE					
						
COPIES TO	MATL SPEC COVER: THERMOPLASTIC HOLDER: THERMOPLASTIC DFK CONTACTS: COPPER ALLOY					
1 9 18	FINISH					
2 10 19	-					
3 12 20						
4 13 21	DRW	FYUE	DATE 15/Feb/16 SCALE 5:1			
5 14 23	CHK		DATE SUPER DR			
6 15 33	APPD		DATE FINSH GOOD WT			
7 16 43						
8 17 53						
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-mK)						
DIMENSION	0.5 - 3	UP TO 3	UP TO 6	UP TO 30	UP TO 120	UP TO 1000
TOLERANCE	+0.1	+0.1	+0.2	+0.3	+0.5	
3RD ANGLE PROJECTION						
				TITLE		
				FH2- BLOCKHOLDER, COMPLETE		
				REVISION		DRWG. NO.
				A		178.6105.0001
CHICAGO, USA 773-628-1000				OUTLINE		

METRIC
ASSEMBLY

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED (rev C)