


PART No.	WIRE GA. / COLOR	"A"
0FNY0001ZXJ	#14 BLACK	203.2±5 (8.0)



DETAIL B



- NOTES:
1. MAX FUSE RATING: 20A, 32VDC.
 2. MAX. OPERATING TEMPERATURE: 80°C.
 3. WIRE: COPPER STRANDED, UL 1015.
 4. CONTACTS: C2680 ALLOY.
 5. CRIMP: MUST MEET USCAR 21 STANDARD.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

CPK DENOTES CRITICAL CHARACTERISTICS.
 CPK DENOTES CPK DIMENSIONS--MINIMUM CPK VALUE
 DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT IS TO BE DETERMINED BY THE DRAWING OR BY THE INSTRUCTIONS.
 CPK DENOTES CP DIMENSIONS--MINIMUM CP VALUE DENOTES CP VALUE WITHIN THE DIMENSIONAL LIMITATIONS OF PROCESS PERFORMANCE AND INITIALLY LOCATED TO A DIMENSION FOR MAXIMUM TOOL LIFE.

COPIES TO		MATERIAL SPEC		FINISH	
1	9	DRW	DWM	DATE	09/05/08
2	10	CHK		DATE	
3	12	APPD		DATE	
4	13			SCALE	1=1
5	14			SUPER DRW	
6	15			RAW STK WT	LBS/M
7	16			TOLERANCE UNLESS OTHERWISE SPECIFIED	
8	17			TWO PLACE DEC ±.01 FRACTION ±	
				THREE PLACE DEC ±.005 ANGULAR ±1°	
TITLE					
FUSEHOLDER, IN LINE (WITH FUSE)					

LTR	REVISION	CHK	APD
A	000490ER-RELEASED 9/05/08		

REVISION: A

DRWG. NO. 0FNY0001ZXJ

OUTLINE

DES PLAINES, ILLINOIS 60016

CONTROLLED DOCUMENT