





THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	GCF #524724 INITIAL RELEASE. D.SILVA	1/25/2022	L.ARGIL






- NOTE:
1. THIS IN-LINE FUSEHOLDER IS DESIGNED TO TURN ONE SLOT INTO TWO.
  2. MAX. INSTALLATION RATING UP TO 10 AMPS.
  3. BUTT SPLICE CONNECTORS PULL-OUT FORCE IS 15.0 KGF MIN.
  4. FUSE PULL OUT FORCE TO BE 3.5 TO 7.0 KGF.

NO.	COMPONENT NO.	COMPONENT NAME	QTY	U
-----	---------------	----------------	-----	---

TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-mK)												
.5 to 3	>3 to 6	>6 to 30	>30 to 120	>120 to 400								ANGLE
±0.10	±0.10	±0.20	±0.30	±0.50								NONE

DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.

PER CH-NP20-0008 PROCEDURE

	FIT/ FUNCTION CRITICAL CHARACTERISTICS
	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE
	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

NAME	DATE	 Expertise Applied   Answers Delivered	
DRAWN	D.SILVA		
CHECKED	-	TITLE	
	-		
FORM NO:	CVP-PE40-0003 REV B	HOLDER MICRO 2 ADD-A-CIRCUIT	
THIRD ANGLE PROJECTION			
	SIZE	DWG. NO.	REV.
DO NOT SCALE DRAWING	B	OUTLINE	A
SCALE 1:1			SHEET 1 OF 1