



NOTES:

- MATERIAL:
 BASE: UL94V-0 GLASS FILLED NYLON
 STUDS: M5
 NUTS: ZINC-PLATED NYLOCK NUT
- TORQUE RATING: 5±1 Nm
- FUSE RATING: 30-200A
- WIRE SIZE: 14-4 AWG (2.5mm²-20mm²)
- TEMPERATURE RATING: -40°C TO 125°C

PACKAGING NOTES:

- PARTS ARE PACKED 50 PC PER BAG, 10 BAGS PER BOX.

METRIC
ASSEMBLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS.
 DIMENSIONS IN BRACKETS [] ARE INCHES

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

⊙ DENOTES CRITICAL CHARACTERISTICS.
 CPK DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
 Ⓢ DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
 CP DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				

LTR	DATE	REVISION	CHK	APD
A	05/16/11	502090ERA-RELEASE	OPL	

COPIES TO		MATL SPEC										
1	9	18	FINISH									
2	10	19	SCALE 1:1									
3	12	20	DRW	OPL	DATE	05/16/11	SCALE	SUPER DR				1:1
5	14	23	CHK	DATE								
6	15	33	APPD	DATE								
7	16	43	FINISH GOOD WT									
8	17	53	GRAMS/PIECE									
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-mK)			UP TO	OVER	UP TO	OVER	UP TO	OVER	UP TO	OVER		
DIMENSION	0.5 - 3	3 - 6	±0.1	±0.2	±0.3	±0.5	±0.3	±0.5	±0.3	±0.5		
TOLERANCE	3RD ANGLE PROJECTION											

TITLE: BASE FOR MIDI INLINE HOLDER, W/M5 BOLTS

REVISION DRWG. NO. A OL-498921-2

OUTLINE

Littelfuse
DES. PLAINES, ILLINOIS 60016