



- NOTES:
1. MATERIAL: COPPER C1100, TIN PLATED
 2. UNLESS OTHERWISE NOTED, BURR SHALL NOT EXCEED 10% OF THE RAW MATERIAL THICKNESS AT ANY LOCATION
 3. PART TO BE CLEAN, DEGREASED, FREE OF CONTAMINATION

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.



DENOTES CRITICAL CHARACTERISTICS.

CPK

DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE



DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS

CP

DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

BILL OF MATERIAL

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M

LTR	DATE	REVISION	CHK	APD
A	06/26/13	50B674ERA-RELEASE FYUE		
B	07/10/13	50B881ECA-THICKNESS 2.3 WAS 2.0 FYUE		

COPIES TO	MATL SPEC
1 9 18	SEE NOTE
2 10 19	
3 12 20	FINISH SEE NOTE
4 13 21	DRW DATE 06/26/13 SCALE 1:1
5 14 23	FYUE
6 15 33	CHK DATE SUPER DR
7 16 43	APPD DATE FINISH GOOD WT
8 17 53	GRAMS/PIECE

TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)	UP TO	OVER	UP TO	OVER	UP TO	OVER
DIMENSION	0.5 - 3	3 - 6	6 - 30	30 - 120	120 - 400	400 - 1000
TOLERANCE	+0.05	+0.05	±0.1	±0.15	±0.2	±0.3

3RD ANGLE PROJECTION

TITLE 5 POSITION BUS BAR - FLEX MIDI HOLDER

REVISION B

DRWG. NO. OL-882-267-005

Littelfuse
CHICAGO, USA 773-628-1000