



PART No.	BODY	BODY STYLE	FUSE PROVIDED	FUSE RATING	REMARKS
OFHA0001Z	OFHA0001Z	1	NONE	-----	NOTE 1
OFHA0002Z	OFHA0002Z	2	NONE	-----	NOTE 2
OFHA0003Z	OFHA0001Z	1	0257003.P	3 AMP	NOTE 1
OFHA0004Z	OFHA0001Z	1	0257004.P	4 AMP	NOTE 1
OFHA0005Z	OFHA0001Z	1	0257005.P	5 AMP	NOTE 1
OFHA0075Z	OFHA0001Z	1	025707.5P	7.5 AMP	NOTE 1
OFHA0010Z	OFHA0001Z	1	0257010.P	10 AMP	NOTE 1
OFHA0015Z	OFHA0001Z	1	0257015.P	15 AMP	NOTE 1
OFHA0020Z	OFHA0001Z	1	0257020.P	20 AMP	NOTE 1
OFHA0025Z	OFHA0002Z	2	0257025.P	25 AMP	NOTE 2
OFHA0030Z	OFHA0002Z	2	0257030.P	30 AMP	NOTE 2



BODY STYLE #2



- NOTES:
- FOR OFHA0001Z:
A) MAX. RATING: 20 AMPS, 32 VOLTS AT A MAX. OPERATING TEMPERATURE OF 180° F (82° C).
B) BODY MATERIAL: HIGH TEMPERATURE P.V.C., BLACK.
C) BLACK WIRE LEADS, #16 GAUGE, COPPER STRANDED (19 STRAND/29 GAUGE) PVC INSULATION, 0.016" THICK [0.406mm] AUTOMOTIVE LOW TENSION TYPE GPT/TW PER S.A.E. STRANDED J1128.
 - FOR OFHA0002Z:
A) MAX. RATING: 30 AMPS, 32 VOLTS AT A MAX. OPERATING TEMPERATURE OF 180° F (82° C).
B) BODY MATERIAL: HIGH TEMPERATURE POLYURETHANE, BLACK.
C) ORANGE WIRE LEADS, #12 GAUGE, NOM. O.D. 0.136" [3.5mm], COPPER STRANDED (19 STRAND/25 GAUGE) PVC INSULATION, 0.026" THICK [0.660mm], RATED 300V, TEMP. RANGE: -10°C TO +80°C.

- GENERAL NOTES:
- WIRE LEADS ARE MOLDED INTO FUSEHOLDER BODY.
 - DIMENSIONS IN INCHES, [mm].

NO		COMPONENT NO	DESCRIPTION		QTY/M	U/M
BILL OF MATERIAL						
COPIES TO		MATL SPEC		FINISH		
1	9 18	DRW	JMB	DATE	2/10/99	SCALE 1=1
2	10 19					
3	12 20	CHK		DATE		SUPER DRW
4	13 21					
5	14 23	APPD		DATE		RAW STK WT
6	15 33					LBS/M
7	16 43					
8	17 53					
TOLERANCE UNLESS OTHERWISE SPECIFIED TWO PLACE DEC ±.01 FRACTION ± THREE PLACE DEC ±.005 ANGULAR ±1°						
AUTOFUSE HOLDER, IN LINE (FUSE OPTIONAL)						
LTR		REVISION			CHK	APD
F		39728C- REVISED & REDRAWN ON NEW FORMAT 2/26/99 JMB				

		REVISION	DATE	NO.	SERIES	OUTLINE
		E				OFHA0000Z
		DES PLAINES, ILLINOIS 60016				



DES PLAINES, ILLINOIS 60016

REVISION

E

CHANGE NO.

SERIES OUTLINE

OFHA0000Z

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

DENOTES CRITICAL CHARACTERISTICS.

DENOTES CPK DIMENSIONS.-MINIMUM CPK VALUE

DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT OF PROCESS PERFORMANCE IS LOCATED IN THE INSTRUCTIONS.

DENOTES CP DIMENSIONS.-MINIMUM CP VALUE

DENOTES DIMENSIONS WITHIN THE DIMENSIONAL LIMITATIONS

DENOTES DIMENSIONS WITHIN THE DIMENSIONAL LIMITATIONS FOR MAXIMUM TOOL LIFE.

UNCONTROLLED DOCUMENT