

$\varnothing 30.94 \pm 0.381$   
[ $\varnothing 1.218 \pm 0.015$ ]

$4.75 \pm 0.15$   
[ $0.187 \pm 0.006$ ]

$22.73 \pm 0.89$   
[ $0.895 \pm 0.035$ ]

10.41  
[0.410]

19.18  
[0.755]

$129.16 \pm 1.59$   
[ $5.085 \pm 0.063$ ]

$106.30 \pm 1.59$   
[ $4.185 \pm 0.063$ ]

73.03  
[2.875]

$88.77 \pm 1.59$   
[ $3.495 \pm 0.063$ ]

# REVISION

REV	DATE	DESCRIPTION
A	7/18/23	526718GCP - RELEASE MRY

1				
NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M

## BILL OF MATERIAL

<S> CRITICAL CHARACTERISTIC FOR PART SAFETY/COMPLIANCE

● DENOTES CRITICAL CHARACTERISTICS.

CPK DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE

ST DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.

CP DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.

A

MATL SPEC

FINISH

DRW  
JMoler


DATE  
6/23/2023

SCALE  
NTS

FINISH GOOD WT  
GRAMS/PIECE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [ ] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994

3RD ANGLE  
PROJECTION



TITLE

L70QS 125-200A OUTLINE

**Littelfuse**  
CHICAGO, ILLINOIS 60631

REVISION

A

DRWG NO.

OL-L70QS200

SHEET 1 OF 1