





11	Nut M10	Brass	2	EA
10	Spring washer	Bronze	2	EA
9	Plain washer 10.2x18x2	Brass	2	EA
8	Power stud M10 short	Copper	2	EA
7	Fixing nut for screw	Copper	2	EA
6	Body connector	PBT	1	EA
5	OR ring	Silicon	1	EA
4	Self-tapping screw TCCIC 3x12	Steel	4	EA
3	Top cover	Thermosetting	1	EA
2	Rivet box TGC	Steel	4	EA
1	Box short connector screws	PBT	1	EA
POS.	DESCRIPTION	MATERIAL	Q.TY	U/M



Non sono ammesse modifiche
senza l' approvazione
della "Persona Autorizzata".
*No modify is allowed without the
"Authorized Person" approval.*

- Torque of screw M10 = 19Nm max
- Fix the device with M6 screw and with torque of 6 ± 2 Nm
- (&) Provided in the kit
- (\$) p/N of product
- This product is supplied in the complete kit

- Nominal voltage: 12V or 24V
- Working current main contact: 250A
- Max current main contact: 2000A for 5 sec

DIMENSIONS AND TOLERANCES IN MILLIMETERS, DEFINED ACCORDING TO ISO 1101-2017.						
linear dimensions						
0,5 3	>3 6	>6 30	>30 120	>120 400	>400 1000	>1000 2000
±0,2	±0,3	±0,5	±0,8	±1,2	±2	±3
angle (for range of lengths)						
up to 10	>10 50	>50 120	>120 400			
±1°30'	±1°	±0°30'	±0°15'			
●	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL					
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL					
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE					
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS					
CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE					
NAME			DATE			
DRAWN L. Dal Molin			01-Apr-21			
CHECKED -			-			
-			-			
-			-			
FORM NO. CVP-PE40-0013 REV A			 Littelfuse® Expertise Applied Answers Delivered TITLE ELECTRICAL BMS TGC/MGDE-I ADR2			
FIRST LEGAL PROJECTION						
						
 DO NOT SCALE DRAWING			SIZE: A2		DWG. NO. OL-08075300	
					OUTLINE# REV. A	
DO NOT SCALE DRAWING			SCALE 1:1		SHEET 1 OF 1	

Material and treatments: