


IXFB44N100P

1000 V, 220 mΩ Polar™ HiPerFET™ Power MOSFET

N-Channel Enhancement Mode



Features:

- Unclamped Inductive Switching (UIS) Rated
- Low Package Inductance
 - Easy to Drive and to Protect
- N-Channel Enhancement Mode
- Fast Intrinsic Rectifier
- Avalanche Rated
- Low $R_{DS(on)}$ and Q_G

Advantages:

- Plus 264™ Package for Clip or Spring Mounting
- Space Savings
- High Power Density


Applications:

- Switched-Mode and Resonant-Mode Power Supplies
- DC-DC Converters
- Laser Drivers
- AC and DC Motor Controls
- Robotics and Servo Controls

Product Summary

| Characteristic | Value | Unit |
|----------------|-------|----------|
| V_{DSS} | 1000 | V |
| I_{D25} | 44 | A |
| $R_{DS(on)}$ | 220 | Ω |
| t_{rr} | 300 | ns |

Pinout Diagram (PLUSTO-264)



G: Gate; **D:** Drain; **S:** Emitter; **Tab:** Drain

Maximum Ratings

| Symbol | Characteristics | Conditions | Value | Units |
|-----------|--------------------------------|---|-------------------|-------|
| V_{DSS} | Drain-Source Voltage | $T_J = 25^\circ\text{C}$ to 150°C | 1000 | V |
| V_{DGR} | Drain-Gate Voltage | $T_J = 25^\circ\text{C}$ to 150°C , $R_{GS} = 1\text{ M}\Omega$ | 1000 | V |
| V_{GSS} | Gate-Source Voltage | Continuous | ± 30 | V |
| V_{GSM} | | Transient | ± 40 | |
| I_{D25} | Drain Current | $T_C = 25^\circ\text{C}$ | 44 | A |
| I_{DM} | | $T_C = 25^\circ\text{C}$, Pulse width limited by T_{JM} | 110 | |
| I_{AR} | Avalanche Current | $T_C = 25^\circ\text{C}$ | 22 | A |
| E_{AS} | Avalanche Energy | $T_C = 25^\circ\text{C}$ | 2 | J |
| dV/dt | Reverse Diode dV/dt | $I_S \leq I_{DM}$, $V_{DD} \leq V_{DSS}$, $T_J \leq 150^\circ\text{C}$ | 15 | V/ns |
| P_D | Power Dissipation | $T_C = 25^\circ\text{C}$ | 1250 | W |
| T_J | Operating Junction Temperature | – | -55 to +150 | °C |
| T_{JM} | Maximum Junction Temperature | – | 150 | |
| T_{stg} | Storage Temperature | – | -55 to +150 | |
| T_L | Lead Temperature for Soldering | 1.6 mm (0.062 in.) from case for 10 s | 300 | °C |
| F_C | Mounting Force | – | 30..120 / 6.7..27 | N/lb |
| W | Weight | – | 10 | g |

Thermal Characteristics

| Symbol | Characteristic | Value | | | Unit |
|-------------|--------------------------------------|-------|------|------|------|
| | | Min. | Typ. | Max. | |
| $R_{th,JC}$ | Thermal Resistance, junction-to-case | – | – | 0.10 | °C/W |
| $R_{th,CS}$ | Thermal Resistance, case-to-sink | – | 0.13 | – | °C/W |

Electrical Characteristics – Static ($T_J = 25^\circ\text{C}$ unless otherwise specified)

| Symbol | Characteristic | Conditions | Value | | | Unit |
|--------------|---|--|-------|------|-----------|---------------|
| | | | Min. | Typ. | Max. | |
| BV_{DSS} | Drain-Source Breakdown Voltage | $I_D = 3\text{ mA}$, $V_{GS} = 0\text{ V}$ | 1000 | – | – | V |
| $V_{GS(th)}$ | Gate Threshold Voltage | $I_D = 1\text{ mA}$, $V_{DS} = V_{GS}$ | 3.5 | – | 6.5 | V |
| I_{GSS} | Gate-Source Leakage Current | $V_{DS} = 0\text{ V}$, $V_{GS} = \pm 30\text{ V}$ | – | – | ± 200 | nA |
| I_{DSS} | Drain-Source Current | $V_{DS} = V_{DSS}$, $V_{GS} = 0\text{ V}$ | – | – | 50 | μA |
| | | $V_{DS} = V_{DSS}$, $V_{GS} = 0\text{ V}$, $T_J = 125^\circ\text{C}$ | – | – | 3 | mA |
| $R_{DS(on)}$ | Drain-Source On-Resistance ¹ | $V_{GS} = 10\text{ V}$, $I_D = 0.5 \times I_{D25}$ | – | – | 220 | m Ω |

Note 1: Pulse test, $t \leq 300\ \mu\text{s}$, duty cycle, $d \leq 2\%$

Electrical Characteristics – Dynamic ($T_J = 25^\circ\text{C}$ unless otherwise specified)

| Symbol | Characteristic | Conditions | Value | | | Unit |
|--------------|-------------------------------|--|-------|------|------|----------|
| | | | Min. | Typ. | Max. | |
| g_{fs} | Transconductance ¹ | $V_{DS} = 20\text{ V}, I_D = 0.5 \times I_{D25}$ | 20 | 35 | – | S |
| R_{Gi} | Gate Input Resistance | – | – | 1.4 | – | Ω |
| C_{iss} | Input Capacitance | $V_{GS} = 0\text{ V}, V_{DS} = 25\text{ V}, f = 1\text{ MHz}$ | – | 16.9 | – | nF |
| C_{oss} | Output Capacitance | | – | 1100 | – | pF |
| C_{rss} | Reverse Transfer Capacitance | | – | 184 | – | pF |
| $Q_{g(on)}$ | Total Gate Charge | $V_{GS} = 10\text{ V}, V_{DS} = 0.5 \times V_{DSS},$ $I_D = 0.5 \times I_{D25}$ | – | 305 | – | nC |
| Q_{gs} | Gate-Source Charge | | – | 104 | – | |
| Q_{gd} | Gate-Drain Charge | | – | 126 | – | |
| $t_{d(on)}$ | Turn-on Delay Time | Resistive Switching $V_{GS} = 10\text{ V}, V_{DS} = 0.5 \times V_{DSS},$ $I_D = 0.5 \times I_{D25}, R_{G(ext)} = 1\ \Omega$ | – | 60 | – | ns |
| t_r | Rise Time | | – | 68 | – | |
| $t_{d(off)}$ | Turn-off Delay Time | | – | 90 | – | |
| t_f | Fall Time | | – | 56 | – | |

Note 1: Pulse test, $t \leq 300\ \mu\text{s}$, duty cycle, $d \leq 2\%$

Source-Drain Diode Characteristics ($T_J = 25^\circ\text{C}$ unless otherwise specified)

| Symbol | Characteristic | Conditions | Value | | | Unit |
|----------|------------------------------------|---|-------|------|------|---------------|
| | | | Min. | Typ. | Max. | |
| I_S | Continuous Diode Forward Current | $V_{GS} = 0\text{ V}$ | – | – | 44 | A |
| I_{SM} | Diode Pulse Current | Repetitive, Pulse width limited by T_{JM} | – | – | 176 | A |
| V_{SD} | Diode Forward Voltage ¹ | $I_F = I_S, V_{GS} = 0\text{ V}$ | – | – | 1.5 | V |
| t_{rr} | Reverse Recovery Time | $I_F = 22\text{ A}, -di/dt = 100\text{ A}/\mu\text{s},$ $V_r = 100\text{ V}$ | – | – | 300 | ns |
| Q_{rm} | Reverse Recovery Charge | | – | 2.5 | – | μC |
| I_{rm} | Reverse Recovery Current | | – | 17.0 | – | A |

Note 1: Pulse test, $t \leq 300\ \mu\text{s}$, duty cycle, $d \leq 2\%$

Characteristic Curves

Fig. 1. Output Characteristics @ $T_J = 25^\circ\text{C}$




Fig. 2. Extended Output Characteristics @ $T_J = 25^\circ\text{C}$




Fig. 3. Output Characteristics @ $T_J = 125^\circ\text{C}$




Fig. 4. $R_{DS(on)}$ Normalized to $I_D = 22\text{A}$ Value vs. Junction Temperature




Fig. 5. $R_{DS(on)}$ Normalized to $I_D = 22\text{A}$ Value vs. Drain Current




Fig. 6. Maximum Drain Current vs. Case Temperature




Fig. 7. Input Admittance




Fig. 8. Transconductance




Fig. 9. Forward Voltage Drop of Intrinsic Diode




Fig. 10. Gate Charge




Fig. 11. Capacitance






Fig. 12. Maximum Transient Thermal Impedance



Part Outline Drawing (PLUS TO-264)



| Symbol | Inches | | | Millimeters | | |
|--------|-----------|---------|-------|-------------|---------|-------|
| | Min. | Typical | Max. | Min. | Typical | Max. |
| A | 0.185 | – | 0.209 | 4.70 | – | 5.31 |
| A1 | 0.102 | – | 0.118 | 2.59 | – | 3.00 |
| b | 0.037 | – | 0.055 | 0.94 | – | 1.40 |
| b1 | 0.087 | – | 0.102 | 2.21 | – | 2.59 |
| b2 | 0.110 | – | 0.126 | 2.79 | – | 3.20 |
| c | 0.017 | – | 0.029 | 0.43 | – | 0.74 |
| D | 1.007 | – | 1.047 | 25.58 | – | 26.59 |
| E | 0.760 | – | 0.799 | 19.30 | – | 20.29 |
| e | 0.215 BSC | | | 5.46 BSC | | |
| L | 0.779 | – | 0.842 | 19.79 | – | 21.39 |
| L1 | 0.087 | – | 0.102 | 2.21 | – | 2.59 |
| Q | 0.240 | – | 0.256 | 6.10 | – | 6.50 |
| Q1 | 0.330 | – | 0.346 | 8.38 | – | 8.79 |
| ØR | 0.155 | – | 0.187 | 3.94 | – | 4.75 |
| ØR1 | 0.085 | – | 0.093 | 2.16 | – | 2.36 |

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.



Part of:

