




ARTIKELNUMMER ARTICLE-No.	B1 IN mm	B2 IN mm	H1 IN mm	H2 IN mm	mm2
178.6116.100_	3.0	4.2	2.8	3.9	0.5 - 1
178.6116.2501/2	3.5	5.1	3.85	4.9	1.5 - 2.5
178.6116.2508	4.1	5.3	3.8	5.3	1.5 - 2.5
178.6116.400_	5.1	6.9	4.7	6.7	2.5 - 4
178.6116.600_	6.2	8.1	5.7	7.3	4 - 6

TOLERANZ DER TABELLENMAßE $\pm 0.2 \text{ mm}$.
 CHART TOLERANCES $\pm 0.2 \text{ mm}$.

ALLGEMEINTOLERANZEN
GENERAL TOLERANCES
DIN ISO 2768-m



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS.
DIMENSIONS IN BRACKETS [] ARE INCHES

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

© DENOTES CRITICAL CHARACTERISTICS.

CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
-----	--

ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
----	---

CP

DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

METRIC COMPONENT

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M

[illegible]