




THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

REVISIONS					
REV.	DESCRIPTION	DATE	GCF / ECR	DESIGNED	APPROVED
A	Initial Release	30-Jan-23		L.Dal Molin	M.Tinto



PRESCRIPTION


£: Mold code

\$: Molding footprint number

&: Manufacture date

*: Material symbol

1	Protection ext. 2 holes	Polyamide	1
POS.	DESCRIPTION	MATERIAL	Q.ty

DIMENSIONS AND TOLERANCES IN MILLIMETERS, DEFINED ACCORDING TO ISO 1101-2017.						
linear dimensions						
0,5	>3	>6	>30	>120	>400	>1000
3	6	30	120	400	1000	2000
±0,2	±0,3	±0,5	±0,8	±1,2	±2	±3
angle (for range of lengths)						
up to	>10	>50	>120	>120	>120	>120
10	50	120	400	400	400	400
±1°30'	±1°	±0°30'	±0°15'	±0°15'	±0°15'	±0°15'
●	FIT/ FUNCTION CRITICAL CHARACTERISTICS SYMBOL					
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL					
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE					
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE.PROCEDURE FOR MEASUREMENTAND TRACKINGTO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS					
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE					
	NAME	DATE	 Expertise Applied Answers Delivered			
DRAWN	L.Dal Molin	30 Jan 2023				
CHECKED	-	-				
	-	-				
	-	-	TITLE			
FORM NO: CVP-PE40-0013 REV A			PROTECTION EXTERNAL 2 HOLES			
FIRST ANGLE PROJECTION						
			SIZE: A3	DWG. NO. OL-00902900	OUTLINE REV. A	
DO NOT SCALE DRAWING			SCALE 1:1		SHEET 1 OF 1	