


CHARACTERISTICS:

- Nominal working tension: 14.5 V - 28.5 V
- Nominal working current: 5 A - 10 A
- Nominal working current main contact: 250 A
- Nominal max current main contact: 2000 A for 5 sec

DIMENSIONS AND TOLERANCES IN MILLIMETERS, DEFINED ACCORDING TO ISO 1101:2017						
linear dimensions						
0,5 3	>5 3	>6 3	>30 120	>100 400	>1000 2000	>10000 20000
±0,2	±0,3	±0,5	±0,8	±1,2	+2	+3
angle (for measurement lengths)						
up to 10°	up to 50°	up to 90°	up to 120°	up to 150°	up to 210°	
● 1'			● 30'	● 30'	● 10'15'	
● 1' / FUNCTION CRITICAL CHARACTERISTICS SYMBOL						
<S> SAFETY COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL						
CPK DENOTES CPK DIMENSIONS MINIMUM CPK VALUE						
 DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE PROCEDURE (FOR MEASUREMENT VALUE) TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS						
CP DENOTES CP DIMENSIONS - MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL TOLERANCES SHOWN ON DRAWING AND INITIALLY LOCATED TO CORRESPOND TO MAXIMUM TOOL LIFE						
NAME		DATE		 Expertise Applied Answers Delivered		
DRAWN: L. Del Mar		09-Sep-21				
CHECKED:						
FORM NO. CDP-PK63430 REV. A FIRST ANGLE PROJECTION				TITLE IGC/MS14 12-24V		
				SIZE: A1 DWG. NO. OL-08075063		
DO NOT SCALE DRAWING				SCALE 1:1 SHEET 1 OF 1		



SAP drawing number: