






Spare part cod 00226200
Protection open 70mmq



Screw the connector nut
with a pair of 7 ± 1 Nm



- Nominal operating voltage: 12 ÷ 24 V
- Max continuous current on contacts: 250 A at 23°C
- Max current short duration on contacts: 2000 A at 23°C for 30 sec.

- Number of electrical and mechanical operations: 50.000
- Locking torque nuts M10/M12: 20 Nm

- We suggest to fix the TGC to the structure by screws M8 UNI 5931:1984 and plane washers 8.4 x 17 UNI 6592:1969 under head
- (*): Data of production
- The distance between plunger bridge and fix contact must be minimum 2 mm

Material and treatments:

DIMENSIONS AND TOLERANCES IN MILLIMETERS, DEFINED ACCORDING TO ISO 1101:2017						
linear dimensions						
0,5 3	>3	>6	>30	>120	>400	>1000
±0,2	±0,3	±0,5	±0,8	±1,2	±2	±3
angle (of face lengths)						
up to 10°	>10° 50	>50 120	>120 400	>400 1000	>1000 400	
±1'		±1'		±0°30'	±0°15'	
● IT /FUNCTION CRITICAL CHARACTERISTICS SYMBOL						
< S > SAFETY COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL						
CPK DENOTES CPK DIMENSIONS MINIMUM CPK VALUE						
(ST) DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE (CAPABILITY FOR MEASUREMENT) TRACKING SHOULD BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS						
CP DENOTES CP DIMENSIONS - MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO 40 FOR MAXIMUM TOOL LIFE						
NAME		DATE		 Littelfuse® Expertise Applied Answers Delivered		
DRAWN / L. Del Mar		27/05/2019				
CHECKED						
FORM NO. CDP-REF4603.0 REV. A FIRST ANGLE PROJECTION				TITLE GENERAL ELECTRICAL MAIN SWITCH IGC/RMC/DE 24V A1 DWG. NO. OI-080977460 A		
 DO NOT SCALE DRAWING				SHEET 1 OF 1 SHEET 1 OF 1		

