



## QQX2.E71639 Electrically Isolated Semiconductor Devices - Component

[Page Bottom](#)

### Electrically Isolated Semiconductor Devices - Component

[See General Information for Electrically Isolated Semiconductor Devices - Component](#)

#### LITTELFUSE/TECCOR

E71639

SUITE 500

8755 W HIGGINS RD

CHICAGO, IL 60631 USA

**Electrically Isolated Semiconductor Devices, GH Type, package "GH-X"**, Model(s) MG1225H-XN2MM, MG1250H-XN2MM, MG1275H-XN2MM

**Electrically Isolated Semiconductor Devices, GH Type, package "GH-XB"**, Model(s) MG1215H-XBN2MM, MG1225H-XBN2MM, MG1240H-XBN2MM

**Electrically isolated semiconductor devices, GS type**, Model(s) MG12150S-BN2MM, MG12150S-DEN2MM, MG17100S-BN4MM, MG1750S-BN4MM, MG1775S-BN4MM

**Electrically Isolated Semiconductor Devices, GW Type, package "GW-X"**, Model(s) MG12150W-XN2MM, MG1275W-XN2MM

**Electrically Isolated Semiconductor Devices, GW Type, package "GW-XB"**, Model(s) MG1250W-XBN2MM, MG1275W-XBN2MM

**Electrically Isolated Semiconductor Devices, GWB Type, package "GWB-B"**, Model(s) MG06600WB-BN4MM, MG12225WB-BN2MM, MG12300WB-BN2MM, MG12450WB-BN2MM, MG12600WB-BR2MM, MG17225WB-BN4MM, MG17300WB-BN4MM, MG17450WB-BN4MM

**Electrically Isolated Semiconductor Devices GW Type, package "GW-X"**, Model(s) MG12100W-XN2MM

**Electrically-isolated semiconductor devices**, Model(s) MD08110A-\*M2MM#, MD08130A-\*M2MM#, MD08130S-\*M2MM#, MD08160S-\*M2MM#, MD08180S-\*M2MM#, MD08200S-\*M2MM#, MD08220S-\*M2MM#, MD0850A-\*M2MM#, MD0890A-\*M2MM#, MD10110A-\*M2MM#, MD10130A-\*M2MM#, MD10130S-\*M2MM#, MD10160S-\*M2MM#, MD10180S-\*M2MM#, MD10200S-\*M2MM#, MD10220S-\*M2MM#, MD1050A-\*M2MM#, MD1090A-\*M2MM#, MD12110A-\*M2MM#, MD12130A-\*M2MM#, MD12130S-\*M2MM#, MD12160S-\*M2MM#, MD12180S-\*M2MM#, MD12200S-\*M2MM#, MD12220S-\*M2MM#, MD1250A-\*M2MM#, MD1290A-\*M2MM#, MD14110A-\*M2MM#, MD14130A-\*M2MM#, MD14130S-\*M2MM#, MD14160S-\*M2MM#, MD14180S-\*M2MM#, MD14200S-\*M2MM#, MD14220S-\*M2MM#, MD1450A-\*M2MM#, MD16110A-\*M2MM#, MD16130A-\*M2MM#, MD16130S-\*M2MM#, MD16160S-\*M2MM#, MD16180S-\*M2MM#, MD16200S-\*M2MM#, MD16220S-\*M2MM#, MD1650A-\*M2MM#, MD1690A-\*M2MM#, MD18110A-\*M2MM#, MD18130A-\*M2MM#, MD18130S-\*M2MM#, MD18160S-\*M2MM#, MD18180S-\*M2MM#, MD18200S-\*M2MM#, MD18220S-\*M2MM#, MD1850A-\*M2MM#, MD1890A-\*M2MM#, MD20110A-\*M2MM#, MD20130A-\*M2MM#, MD20130S-\*M2MM#, MD20160S-\*M2MM#, MD20180S-\*M2MM#, MD20200S-\*M2MM#, MD20220S-\*M2MM#, MD2050A-\*M2MM#, MD2090A-\*M2MM#, MG06100S-BN4MM, MG06100S-BR1MM, MG06150S-BN4MM, MG06200D-BR1MM, MG06200S-BN4MM, MG06300D-BN1MM, MG06300D-BN4MM, MG06400D-BN1MM, MG06400D-BN4MM, MG0675S-BN4MM, MG12100D-BA1MM, MG12100S-BA1MM, MG12100S-BN2MM, MG12100S-BN3MM, MG12150D-BA1MM, MG12150D-BN3MM, MG12150S-BA1MM, MG12150S-BN2MM, MG12200D-BA1MM, MG12200D-BN2MM, MG12200D-BN3MM, MG12300D-BA1MM, MG12300D-BN2MM, MG12300D-BN3MM, MG12400D-BN2MM, MG1250S-BA1MM, MG1275S-BA1MM, MG1275S-BN3MM, MMD1490A-\*M2MM#

**Electrically-isolated semiconductor devices, GD type**, Model(s) MG17100D-BN4MM, MG17150D-BN4MM, MG17200D-BN4MM, MG17300D-BN4MM

**Power switching semi-conductors providing 2500 V ac isolation, Package FASTPAK**, Model(s) Q6025P5, Q6035P5, Q8025P5, Q8035P5

**Power switching semi-conductors providing a minimum 1600 V rms isolation voltage rating, package press-fit**, Model(s) Q series, followed by 20, 40, 50, 60, followed by 25, 40, may be followed by C or D, may be followed by additional suffixes.#

**Power switching semi-conductors providing a minimum 1600 V rms isolation voltage rating, package swedges**, Model(s) Q20, Q40, Q50, Q60 series, followed by 04, 06, 08, 10, 15, 25, may be followed by A, B, V, X, Y or Z, may be followed by additional suffixes.#

**Power switching semi-conductors providing a minimum 1600 V rms isolation voltage rating, power SCRs,** Model(s) S series, followed by 03, 05, 10, 20, 40, 60, followed by 06, 08, 10, 15, 25, followed by A, B, or X, may be followed by additional suffixes.#

S series, followed by 03, 05, 10, 20, 40, 60, followed by 25, 35, may be followed by C or D.#

**Power switching semi-conductors providing a minimum 1600 V rms isolation voltage rating, sensitive gate SCRs,** Model(s) S series, followed by 03, 05, 10, 20, 40, followed by 06, 08, 10, followed by BS, may be followed by additional suffixes.#

**Power switching semi-conductors providing a minimum 2500 V rms isolation voltage rating, Package FASTPAK,** Model(s) Q series, followed by 20, 30, 40, 50, 60, 70, or 80, followed by 25, 35 or 40, followed by P, may be followed by additional suffixes.#

S series, followed by 03, 05, 10, 20, 40, 60, 70, or 80, followed by 65, followed by P, may be followed by additional suffixes.#

**Power switching semi-conductors providing a minimum 2500 V rms isolation voltage rating, Package SOT227, electrically-isolated semiconductor devices,** Model(s) MS0690J series, may be followed by suffixes.#

**Power switching semi-conductors providing a minimum 2500 V rms isolation voltage rating, Package TO-218, high current triacs,** Model(s) Q or HQ series, followed by 20, 40, 50, 60, 70, 80 or K0, followed by 25 or 40, followed by K, may be followed by additional suffixes.#

**Power switching semi-conductors providing a minimum 2500 V rms isolation voltage rating, Package TO-218, power rectifiers,** Model(s) D series, followed by 05, 10, 20, 40, 50, 60, 70, 80, K0, followed by 35, 50 or 65, followed by K, may be followed by additional suffixes.#

**Power switching semi-conductors providing a minimum 2500 V rms isolation voltage rating, Package TO-218, silicon controlled rectifiers,** Model(s) S or HS series, followed by 05, 10, 20, 40, 50, 60, 70, 80, K0, K2, or K6, followed by 35, 50, 55, or 65, followed by K, may be followed by additional suffixes.#

**Power switching semi-conductors providing a minimum 2500 V rms isolation voltage rating, Package TO-218X, high current triacs,** Model(s) Q or HQ Series, followed by 20, 40, 50, 60, 70, 80 or K0, followed by 25 or 40, followed by J, may be followed by additional suffixes.#

**Power switching semi-conductors providing a minimum 2500 V rms isolation voltage rating, Package TO-218X, power rectifiers,** Model(s) D series, followed by 05, 10, 20, 40, 50, 60, 70, 80, K0, followed by 35, 50 or 65, followed by J, may be followed by additional suffixes.#

**Power switching semi-conductors providing a minimum 2500 V rms isolation voltage rating, Package TO-218X, silicon controlled rectifiers,** Model(s) S or HS series, followed by 05, 10, 20, 40, 50, 60, 70, 80, K0, followed by 35, 50 or 65, followed by J, may be followed by additional suffixes.#

**Power switching semi-conductors providing a minimum 2500 V rms isolation voltage rating, Package TO-220,** Model(s) LTL series, followed by 04, 08, 12, 16, or 25, followed by 100, 200, 400, 500, 600, 700, or 800, followed by TH, SH, CH, BH, T, S, C, or B, may be followed by two additional letters.#

Q1359, Series Q or HQ followed by 20, 40, 50, 60, 70, 80, K0, or K2, followed by 01, 03, 04, 06, 08, 10, 12, 15, 16, 25, or 30, followed by L, may be followed by additional suffixes.#

S or HS series, followed by 03, 05, 10, 20, 40, 60, 70, 80, K0, K2, or K6, followed by 01, 03, 06, 08, 10, 12, 15, 20, or 25, followed by L, may be followed by additional suffixes.#

SRR series, followed by 40, 60, 70, 80, or K0, followed by 01, 03, 06, 08, 10, 12, 15, 16, 20, 25, or 40, followed by L, may be followed by additional suffixes.#

**Power switching semi-conductors providing a minimum 2500 V rms isolation voltage rating, Package TO-220, logic triacs,** Model(s) L series, followed by 20, 40, 60, or 70, followed by 01, 04, 06, 08, followed by L, may be followed by additional suffixes.#

**Power switching semi-conductors providing a minimum 2500 V rms isolation voltage rating, Package TO-220, power rectifiers,** Model(s) D series, followed by 20, 40, 60, 80, K0, followed by 15, 20, 25, followed by L, may be followed by additional suffixes.#

Note - Where \* may be B, DK or DA, and # part numbers may be preceded by prefixes for customer requirements.

Marking: Company name or tradename "Company name or stylized T and series designation" and model designation.

Last Updated on 2016-06-24

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2016 UL LLC".