

2506-L	10.000 [254.00]	10.000 [254.00]	0.375 [9.52]	0.375 [9.52]	NONE	NONE	16 GA GPT [1.0 mm sq]	BLACK	0.035 [0.89]
2506-K	18.000 [457.20]	18.000 [457.20]	0.375 [9.52]	0.375 [9.52]	NONE	NONE	16 GA GPT [1.0 mm sq]	BLACK	0.035 [0.89]
2506-J	36.000 [914.40]	36.000 [914.40]	0.375 [9.52]	0.375 [9.52]	NONE	NONE	16 GA GPT [1.0 mm sq]	BLACK	0.035 [0.89]
2506-H	SEE	NOTE	2						0.035 [0.89]
2506-G	10.000 [254.00]	10.000 [254.00]	0.250 [6.35]	0.250 [6.35]	31104	31104	18 GA GPT [0.8 mm sq]	BLACK	0.035 [0.89]
2506-F	10.000 [254.00]	24.000 [609.60]	0.250 [6.35]	0.250 [6.35]	3116	3116	16 GA GPT [1.0 mm sq]	BLACK	0.035 [0.89]
2506-E	6.000 [152.40]	10.000 [254.00]	0.250 [6.35]	0.250 [6.35]	2506-10	2506-10	16 GA GPT [1.0 mm sq]	BLACK	0.035 [0.89]
2506-D	12.000 [304.80]	12.000 [304.80]	0.375 [9.52]	0.375 [9.52]	NONE	NONE	16 GA GPT [1.0 mm sq]	BLACK	0.025-0.032 [0.63-0.81]
2506-C	12.000 [304.80]	12.000 [304.80]	0.375 [9.52]	0.375 [9.52]	NONE	NONE	16 GA GPT [1.0 mm sq]	BLACK	0.047 [1.19]
2506-B	12.000 [304.80]	12.000 [304.80]	0.375 [9.52]	0.375 [9.52]	NONE	NONE	16 GA GPT [1.0 mm sq]	BLACK	0.021 [0.53]
2506-A	12.000 [304.80]	12.000 [304.80]	0.375 [9.52]	0.375 [9.52]	NONE	NONE	16 GA GPT [1.0 mm sq]	BLACK	0.090-0.100 [2.28-2.54]
2506	8.000 [203.20]	8.000 [203.20]	0.375 [9.52]	0.375 [9.52]	NONE	NONE	16 GA GPT [1.0 mm sq]	BLACK	0.035 [0.89]
PT NO	A	B	C	D	TERM A	TERM B	TYPE BOTH WIRES	COLOR PANEL	THK

Tolerances: Unless otherwise specifically noted, the following are default tolerances:

- Splices Decimal Dimensions ± 0.01
- Splices Fractional Dimensions ± 0.005
- Angular Dimensions ± 0.5 Deg
- Holes: Refer to equivalent English Dimension Tolerance
- >>> NOTE: All tolerances are Also Cumulative.

Dimensional Units: All dimensions are expressed in inches unless noted. Dimensions in brackets are expressed in millimeters.

ASST - as Specified, a Non-Toleranced Reference Dimension, shown for identification purposes only.

Used On
or Ref:

Scale: 1:1

Drawn By: RLM

Date Drawn: 7/21/48

Responsible Engineer: NA

Pg. 2 of 2

DISCLAIMER/NOTICE: This Engineering Drawing, and the information contained herein, is proprietary to Cole Hersee Company and may not be disclosed, reproduced, or in any way transmitted or communicated to any other party without the express written consent of an authorized representative of Cole Hersee Company.

DESIGN CONTROL: It is the responsibility of the individual using/interpreting this drawing to ensure that the stated design notation level agrees with the revision level of the Controlled Document (Master Drawing). This is a **NON-CONTROLLED DOCUMENT** unless otherwise specifically noted.

DO NOT SCALE: Dimensional variation may occur during printing/ reproduction.

Special Characteristics:



Critical Characteristics relating to Safety and/or Regulatory Compliance



Significant Characteristics relating to Process Control (SPC)



Control Dimension relating to Form - Fit - Function as defined by Cole Hersee Company and/or the Customer

Note that the identification of any Characteristics as being "Special" does not alter the requirement that ALL specified dimensions & tolerances must be met.



Cole Hersee Co.

20 Old Colony Ave., South Boston, MA, 02127
Phone 617-268-2100 Web www.colehersee.com

Description:

SOCKET ASSEMBLY

Drawing/
Part No.

2506

Current Rev.
SEE PG. 1
FOR REV.